

PowerLife™ Standard Wireless Coils, Powered with NuCurrent® Technology

Coil	Frequency Rx / Tx	Dimensions (mm)	Maximum Thickness W/ Ferrite (mm)	Ferrite Material
1461794011	Low Both	Rx: 25.10 Dia. Tx: 27.00 Dia.	Rx: 0.54 Tx: 3.70	Rx: Flex Tx: Wire
1461790001	Low Rx	50.00 x 43.00	0.63	Flex
1461791001	Low / Dual Rx	43.00 x 31.00	0.53	Flex
1461791011	Low / Dual Rx	47.00 x 40.00	0.57	Flex
1461794001	Low / Dual + NFC Rx	65.50 x 48.40	0.57	Flex
1461798001	High Rx	71.51 x 56.30	1.15	FR4
1461798011	High Rx	26.50 Dia.	0.53	Flex
1461798021	High Rx	35.02 Dia.	0.685	Flex
1461792001	Tri-Mode Rx	64.70 x 53.60	1.60	FR4

