

	Product	Power Range	Size	Key Features	Warranty	Agency Approvals	
AC	VEGA (Modular)	450W - 900W	10.6 x 5 x 2.5	Multiple outputs 1-10, 1.8V-62V Power density No minimum load Mil Standard Shock & Vibe	3 years	IEC60950 = Info tech equip. IEC60601 = Medical	
	VEGA LITE (Modular)	550W, 750W	10.6 x 5 x 2.5	Multiple outputs 1-10, 1.8V-56V Power density No minimum load More Power for same price as Vega	3 years	IEC60950 = Info tech equip. IEC60601 = Medical	
	NV (Modular)	350W, 960W	Fits 1U form factor	Multiple outputs 1-6 Power density No minimum load leading edge efficiency	3 years	IEC60950 = Info tech equip. IEC60601 = Medical	
	NV (PCB Style)	300W	3 x 5 x 1.25 Fits 1U enclosure 3.75 x 7.25 x 1.34	Multiple outputs 1-5 Smaller size, lots of power	3 years	IEC60950 = Info tech equip. IEC60601 = Medical	
	Alpha (Modular)	1000W, 1500W	7 x 2.5 x 11	Multiple Output 1.8V-48V Power density No minimum load	3 years	IEC60950 = Info tech equip. IEC60601 = Medical	
	SWS (Enclosed)	50W - 1000W	Various	Low cost model / superior quality Single output Level B EMI	2 years	IEC60950 = Info tech equip.	
	HWS (Enclosed)	15W - 1500 W	Various	Semi F47 Compliant High efficiency / high density Wide range AC input	Limited lifetime warranty	UL508 = Indust. control equip. UL60950 = Info tech equip.	
	LZSA (Enclosed)	500W - 1500W	Various	Single output -40°C to +71°C operation Rugged mechanical design Superior thermal design Milspec shock and vibe	5 year	UL60950 = Info tech equip.	
	PFE	300W - 1008W	Various	Low profile, small size 100°C baseplate temperature High power density - High efficiency Suitable for conduction cooling Peripheral components required	2 year	UL60950-1 CSA60950-1 (cUL) EN60950-1 CE mark (LVD)	

	Product Family	Power Range	Size	Key Features	Warranty	Agency Approvals	
DC	CC-E	1.5W - 25W	Various	Compact footprint, Through hole or SMT, 5V, 12V, 24V, 48V Input Open Frame, no potting	5 years	UL, CSA, EN, CE	
	PXD	10W - 20W Single Single, Dual	2.0 x 1.0 x 0.4	Industrial standard footprint Six sided shielding, wide range input	1 year	UL, CSA, EN, CE	
	PXE	20W - 30W Single Single, Dual	2.0 x 1.6 x 0.4	Industrial standard footprint Six sided shielding, wide range input	1 year	UL, CSA, EN, CE	
	PXF	40W Single Single, Dual, Triple	2.0 x 2.0 x 0.4	Industrial standard footprint Six sided shielding, wide range input	1 year	UL, CSA, EN, CE	
	PAF	24V - 48V 200V - 400VDC	Full Brick	DC-DC Converter Wide adjustable output range Parallel Pin	2 year	IEC60950 = Info tech equip.	

TDK-Lambda Facts

- ◆ Broad product offering: AC/DC 5W-7500W, DC/DC 1.5W-700W, LAB, EMI Filters
- ◆ Enclosed, open frame, modular, DIN rail, front end, hot swap, Lab, DC/DC
- ◆ #1 Power Mfg in Industrial market
- ◆ Quality: High reliability Warranties 2-5 years, HWS series Lifetime Warranty
- ◆ Pricing: More competitive than ever, as well as Low Cost Solutions
- ◆ Continual new product releases
- ◆ Superior tech support: 1-800-LAMBDA4 / 1-800-526-2324