

SIGNAL SOLUTION KIT PART LOCATOR

Mat'l	Part Number	Bin	Max Cable mm/inches	Z @ 200 KHz	Z @ 500 KHz	Z @ 1 MHz	Z @ 2 MHz	Z @ 5 MHz	----	Closest Solid Equivalent
75	0475181651	R1	4.90 / .193	14	35	66	108	110	----	2675023002
75	0475164281	R5	6.30 / .248	19	49	102	172	110	----	2675540002
75	0475178281	R2	8.70 / .343	18	46	87	115	74	----	2675665702
75	0475167281	R6	9.85 / .388	17	47	92	110	67	----	2675626402
75	0475164181	R3	12.7 / .500	20	58	102	70	50	----	2675102002
75	0475176451	R4	18.0 / .500	30	92	130	81	66	----	----

Mat'l	Part Number	Bin	Max Cable mm/inches	Z @ 10 MHz	Z @ 25 MHz	Z @ 100 MHz	Z @ 250 MHz	Z @ 500 MHz	Z @ 1000 MHz	Closest Solid Equivalent
31	0431173951	Y3	4.90 / .193	60	100	180	208	----	----	2631023002
31	0431164951	Y7	4.90 / .193	100	169	280	247	----	----	2631480002
31	0431164281	Y4	6.30 / .250	105	180	310	240	----	----	2631540002
31	0431167281	Y8	9.85 / .388	81	144	240	270	----	----	2631626402
31	0431164181	Y1	12.7 / .500	100	156	260	260	----	----	2631102002
31	0431176451	Y5	18.0 / .709	130	225	380	370	----	----	2631103002
31	0431173551	Y2	18.5 / .728	69	125	220	310	----	----	----
31	0431177081	Y6	25.15 / .990	125	218	375	340	----	----	2631626202
44	0444173951	W3	4.90 / .193	54	94	150	187	----	----	2643023002
44	0444164951	W7	4.90 / .193	90	144	245	257	----	----	2643480002
44	0444164281	W8	6.30 / .250	95	156	260	270	----	----	2643540002
43	0443164251	W4	6.30 / .250	100	163	275	275	----	----	2643540002
43	0443625006	W1	7.60 / .299	27	50	113	188	----	----	2643625002
43	0443665806	W5	9.20 / .362	23	41	88	122	----	----	2643665802
43	0443167251	W9	9.85 / .388	79	138	225	285	----	----	2643626402
44	0444164181	W2	12.7 / .500	76	138	230	280	----	----	2643102002
43	0443164151	W11	12.7 / .500	90	156	250	305	----	----	2643102002
44	0443806406	W6	15.0 / .591	24	43	90	147	----	----	2643806402
44	0444176451	W10	18.0 / .709	100	175	365	365	----	----	2643103002
44	0444177081	W12	25.15 / .990	115	194	335	330	----	----	2643626202
61	0461178181	B1	4.10 / .161	---	---	115	165	215	300	----
61	0461164951	B3	4.90 / .193	---	---	215	325	385	332	2661480002
61	0461164281	B2	6.30 / .250	---	---	230	355	425	420	2661540002
61	0461167281	B4	9.85 / .388	---	---	175	275	375	400	2661626402
61	0461164181	B5	12.7 / .500	---	---	205	320	435	257	2661102002
61	0461176451	B6	18.0 / .709	---	---	360	480	350	110	----

➡ "Closest Solid Equivalent" parts may provide cost savings compared to Snap-It