

THIN FILM SELECTION GUIDE

Product Type	Series	Case Size (In.)	Power	Resistance	TCR	Tolerance
Precision	KR	0402~2512	1/16W~3/4W	4.7Ω~1.5MΩ	±2ppm/°C~ ±25ppm/°C	±0.01%~ ±1.00%
Low Ohm	KU	0201~2512, 0508~1225	1/20W~3W	10mΩ~10Ω	±50ppm/°C~ ±150ppm/°C	±0.25%~ ±5.00%
High Power Anti-Sulfur	KS	0402~2512	1/10W~1W	1Ω~100KΩ	±10ppm/°C~ ±100ppm/°C	±0.10%~ ±1.00%
General Purpose	KN	0201~2512	1/20W~3/4W	2.49Ω~1.5MΩ	±10ppm/°C~ ±50ppm/°C	±0.10%~ ±1.00%
General Purpose Auto	KN-A	0402~1206	1/16W~1/4W	4.7Ω~1.5MΩ	±10ppm/°C~ ±50ppm/°C	±0.05%~ ±1.00%

Note: This is a product overview, not exact electrical specification. Please refer to product datasheet or contact TFT for the most up-to-date specifications.