


MICRONEL INDUSTRIAL BLOWER U-LINE

Range of Products



Range of Accessories

Contents

Micronel Air Knife	2
Micronel Silent Box	3
Micronel Silencer	3
Micronel Rubber Buffer	4
Micronel Air Filter (Paper)	5
Micronel Filter Cartridge (Paper)	5
Micronel Air Filter (Polyester)	6
Micronel Filter Cartridge (Polyester)	6
Micronel Vacuum Filter VFU1000	7
Micronel Filter Cartridge VFU1000	7
Micronel Vacuum Filter VFU1600	8
Micronel Filter Cartridge VFU1600	8
Micronel Connector-Set M450X	9
Micronel Cable U100X-M16 6-Pol	10
Micronel Choke Module MCM-33/10	11
Micronel Thread Adapter G $\frac{3}{4}$	12
Micronel Outlet Port U97XX-009C3	12
Micronel Outlet Port U97XX-048A3	13
Micronel Inlet Port U97XX-500A9	13



Suitable for applications
in the medical field



Suitable for applications
in the industrial sector

Micronel Air Knife

Blow-off device for a consistent stream of air



Technically and geometrically tailored to the U85 and U100 blowers, the Air Knife allows for a blade-like air flow to be generated, which is ideally suited for removing dirt particles and fluids. Due to being robustly manufactured from stainless steel, the nozzle is rust-free and impervious to detergents.



PROPERTIES

- Substantial cost reduction compared with a compressed air application
- Increased efficiency with cleaning and drying applications
- Precise discharge opening for a consistent air flow
- High air discharge velocity and high compressive force



Micronel Air Knife 40
40 mm



Micronel Air Knife 60
60 mm



Micronel Air Knife 80
80 mm

ORDER SPECIFICATION

Article No.	Product Typ	Size
S4000-00001	Micronel Air Knife 40	40 x 1.5 mm
S4000-00002	Micronel Air Knife 60	60 x 1.2 mm
S4000-00003	Micronel Air Knife 80	80 x 1.2 mm

Suitable blowers for the application

Micronel Radial Blower

U85HL-024KM-42 /-43 /-52 /-53
 U85MX-024KM-42 /-43 /-52 /-53
 U100HL-024KA-4
 U100UL-024KA-4
 U100H4-024KA-4

Micronel Silent Box

Sound attenuation housing with 25 mm inlet and outlet nozzles



The sound attenuation housing made of galvanized sheet steel is equipped with inner foam insulation. Due to this combination of materials, disruptive motor noises are insulated. The 25 mm connectors are readily accessible. Rubber feet provide for further vibration decoupling.



PROPERTIES

- Sound-absorbing walls, reduction of the motor sound level by approx. -6 dB(A)
- Reduction of external vibrations
- The shape geometry enables the internal heat to escape

ORDER SPECIFICATION

Article No.	Product Typ	Size
S1100-00001	Micronel Silent Box	157 x 140 x 97 mm

Suitable blowers for the application	Micronel Radial Blower	U71HL-024KM-43 U85HL-024KH-43 U85MX-024KX-43
--------------------------------------	------------------------	--

Micronel Silencer

Outlet silencer for reducing flow noises



The Micronel Silencer can be used to reduce occurring flow noises. The plastic silencer has a G $\frac{3}{4}$ male thread for the easy and direct assembly on the U100 blower.



PROPERTIES

- Reduction of the flow noise level by up to -10 dB(A)
- Inner insulation, compact shape geometry

ORDER SPECIFICATION

Article No.	Product Typ	Size
S1900-00001	Micronel Silencer	127 x 41 mm

Suitable blowers for the application	Micronel Radial Blower	U100HL-024KA-4 U100UL-024KA-4 U100H4-024KA-4
--------------------------------------	------------------------	--

Micronel Rubber Buffer

Rubber buffer for protecting against vibrations



The buffers are used as vibration damper elements to compensate for vibrations.



PROPERTIES

- Reduction of oscillations and vibrations
- Reduction of mechanical vibration and oscillation noises



Micronel Rubber Buffer M6x16

15 mm
Thread length: 16 mm



Micronel Rubber Buffer M6x15

20 mm
Thread length: 15 mm



Micronel Rubber Buffer M4x6

15 mm
Thread length: 6 mm

ORDER SPECIFICATION

Article No.	Product Typ	Size
S5300-00001	Micronel Rubber Buffer M6x16	Ø 15 mm x 15 mm, 4 Stück
S5300-00002	Micronel Rubber Buffer M6x15	Ø 15 mm x 20 mm, 4 Stück
S5300-00003	Micronel Rubber Buffer M4x6	Ø 15 mm x 15 mm, 4 Stück

Suitable blowers for the application

Micronel Radial Blower

S5300-00001

U100HL-024KA-4
U100UL-024KA-4
U100H4-024KA-4

S5300-00002

U51DL-012KK-42 /-43
U51DL-024KK-42 /-43
U51DL-012KK-52 /-53
U51DL-024KK-52 /-53

S5300-00003

U85HL-024KH-4 /-41 /-42 /-43
U85HL-024KH-5 /-51 /-52 /-53

Micronel Air-Filter (Paper)

Suction filter for protecting the blower from contaminants, filtering degree 5 µm



To avoid impairments due to dirt particles, it is usually necessary to use a suction filter for some applications. The filter ensures that suctioned dirt and particles do not get into the blower.



PROPERTIES

- Protects the blower from dirt and debris
- Replaceable filter cartridge
- G $\frac{3}{4}$ male thread for direct mounting on the U100 blower
- Filter material: Paper
- Large filter surface and minimal pressure loss

ORDER SPECIFICATION

Article No.	Product Typ	Size
S8100-00001	Micronel Air-Filter (Paper)	Ø 120 x 110 mm

Suitable blowers for the application	Micronel Radial Blower	U100HL-024KA-4 U100UL-024KA-4 U100H4-024KA-4
--------------------------------------	------------------------	--

Micronel Filter Cartridge (Paper)

Replacement filter cartridge



The replacement cartridge for the Micronel Air-Filter can be easily replaced in the assembled state without having to replace the entire filter.



PROPERTIES

- Cost-effective replacement filter cartridge
- Simple and quick replacement
- Filter material: Paper

ORDER SPECIFICATION

Article No.	Product Typ	Size
S8100-00002	Micronel Filter Cartridge (Paper)	Ø 110 x 60 mm

Suitable blowers for the application	Micronel Air-Filter (Paper)	S8100-00001
--------------------------------------	-----------------------------	-------------

Micronel Air-Filter (Polyester)

Filter element for protecting the blower from contaminants, filtering degree 10 µm



To avoid impairments due to dirt particles, it is usually necessary to use a rust-free suction filter in the food industry or for industrial parts cleaning applications. The filter ensures that suctioned dirt and particles do not get into the blower.



PROPERTIES

- Replaceable filter cartridge
- G $\frac{3}{4}$ male thread for direct mounting on the U100 blower
- Plastic housing including polyester insert
- Rust-free

ORDER SPECIFICATION

Article No.	Product Typ	Size
S8200-00001	Micronel Air-Filter (Polyester)	Ø 106 x 90 mm

Suitable blowers for the application	Micronel Radial Blower	U100HL-024KA-4 U100UL-024KA-4 U100H4-024KA-4
--------------------------------------	------------------------	--

Micronel Filter Cartridge (Polyester)

Replacement filter cartridge



The replacement cartridge for the Micronel vacuum filter can be easily replaced in the assembled state without having to replace the entire filter.



PROPERTIES

- Cost-effective replacement filter cartridge
- Simple and quick replacement
- Filter material: Polyester

ORDER SPECIFICATION

Article No.	Product Typ	Size
S8200-00002	Micronel Filter Cartridge (Polyester)	Ø 106 x 55 mm

Suitable blowers for the application	Micronel Air-Filter (Polyester)	S8200-00001
--------------------------------------	---------------------------------	-------------

Micronel Vacuum Filter VFU1000

Vacuum filter including paper filter insert, filter fineness 3 µm



To avoid impairments due to dirt particles, it is usually necessary to use a vacuum filter for many vacuum applications. The filter ensures that suctioned dirt and particles do not get into the blower.



PROPERTIES

- Replaceable filter cartridge
- Filter material: Impregnated cellulose paper, filter fineness 3 µm
- Solid filter housing made of steel
- G $\frac{3}{4}$ female thread

NOTE

Thread adapter is needed to connect the filter with the blowers.

ORDER SPECIFICATION

Article No.	Product Typ	Size
S8300-00005	Micronel Vacuum Filter VFU1000	Ø 102 x 91 mm

Suitable blowers for the application	Micronel Radial Blower	U71HL-024KM-41 /-42 /-43 /-52 /-53 U85HL-024KH-41 /-42 /-43 /-52 /-53 U85MX-024KX-41 /-42 /-43 /-52 /-53 U100HL-024KA-4 U100UL-024KA-4 U100H4-024KA-4
--------------------------------------	------------------------	--

Micronel Filter Cartridge VFU1000

Replacement filter cartridge



The replacement cartridge for the Micronel vacuum filter can be easily replaced in the assembled state without having to replace the entire filter.



PROPERTIES

- Cost-effective replacement filter cartridge
- Simple and quick replacement
- Filter material: Impregnated cellulose paper

ORDER SPECIFICATION

Article No.	Product Typ	Size
S8100-00003	Micronel Filter Cartridge VFU1000	Ø 63 x 69 mm

Suitable blowers for the application	Micronel Vacuum Filter VFU1000	S8300-00005
--------------------------------------	--------------------------------	-------------

Micronel Vacuum Filter VFU1600

Vacuum filter including paper filter insert, filter fineness 10 µm



To avoid impairments due to dirt particles, it is usually necessary to use a vacuum filter for many vacuum applications. The filter ensures that suctioned dirt and particles do not get into the blower. Due to the large filter surface, longer product lifetimes are to be expected.



PROPERTIES

- Large filter surface and minimal pressure loss
- Replaceable filter cartridge
- Filter material: Impregnated cellulose paper, filter fineness 10 µm
- Solid filter housing made of steel
- G1¼ female thread

NOTE

Thread adapter is needed to connect the filter with the blowers.

ORDER SPECIFICATION

Article No.	Product Typ	Size
S8100-00006	Micronel Vacuum Filter VFU1600	Ø 135 x 100 mm

Suitable blowers for the application

Micronel Radial Blower

U85HL-024KH-41 /-42 /-43 /-52 /-53
 U85MX-024KX-41 /-42 /-43 /-52 /-53
 U100HL-024KA-4
 U100UL-024KA-4
 U100H4-024KA-4

Micronel Filter Cartridge VFU1600

Replacement filter cartridge



The replacement cartridge for the Micronel vacuum filter can be easily replaced in the assembled state without having to replace the entire filter.



PROPERTIES

- Cost-effective replacement filter cartridge
- Simple and quick replacement
- Filter material: Impregnated cellulose paper

ORDER SPECIFICATION

Article No.	Product Typ	Size
S8100-00004	Micronel Filter Cartridge VFU1600	Ø 98 x 71 mm


Suitable blowers for the application

Micronel Vacuum Filter VFU1600

S8100-00006

Micronel Connector-Set M450X

Molex connector (Mini-Fit, six-pole) with connector cable



Connector cable M450X for U85 and U65 blowers with integrated electronics. The six-pole Molex connector is the counterpart to the blower connector.



PROPERTIES

- Micronel color coding
- Molex connector
- Wiring harness: 300 mm long

ORDER SPECIFICATION

Article No.	Product Typ	Size
M450X-527A9	Micronel Conector-Set M450X	300 mm (+/-15 mm) Stranded wires Ø 1.5 mm ²
Suitable blowers for the application	Micronel Radial Blower	U65M2-024KX-4 U65MX-024KX-4 U85MX-024KX-4 U85HL-024KH-4

Micronel Cable U100X-M16 6-Pol

Six-pole M16 plug with connection cable



Connection cable for all blowers of the U100 series. The six-pole connector cable is completely injection molded and complies with protection class IP67. The cable is available in two connector versions (90° angled and straight).



PROPERTIES

- Plastic injection molding
- M16 cable plug with a straight or 90° angle socket
- Various cable lengths
- Cable thickness: 6.5 mm
- Protection rating IP67 when screwed in
- Wire strength Ø 0.75 mm²



Micronel Cable U100X-M16 6-Pol

Straight plug

Cable thickness: 6.5 mm,

Stranded wires Ø 0.75 mm²

ORDER SPECIFICATION

Article No.	Product Typ	Size
S0400-10001	Micronel Cable U100X-M16 6-Pol	90° angle, 2.5 m length
S0400-10002	Micronel Cable U100X-M16 6-Pol	90° angle, 5.0 m length
S0400-10003	Micronel Cable U100X-M16 6-Pol	90° angle, 10.0 m length
S0400-20001	Micronel Cable U100X-M16 6-Pol	Straight, 2.5 m length
S0400-20002	Micronel Cable U100X-M16 6-Pol	Straight, 5.0 m length
S0400-20003	Micronel Cable U100X-M16 6-Pol	Straight, 10.0 m length

Suitable blowers for the application

Micronel Radial Blower

U100HL-024KA-4
U100UL-024KA-4
U100H4-024KA-4

Micronel Choke Module MCM-33/10

A module providing extra inductance



In order to run a low inductance motor with the Micronel Motor Driver Box MDB-48/10 it is advisory to use the Micronel Choke Module MCM-33/10 to reduce ripple currents. The module comes with mating connectors.



PROPERTIES

- 3 coils with 33 μH inductance for each phase
Currents: 10.7 A_{RMS} / 15 A_{Sat}
- Reduction of ripple currents
- Raises system efficiency
- Reduces unwanted power dissipation and heat generation in the internals of the motor
- Improves EMC
- Extends lifetime of the fan


ORDER SPECIFICATION

Article No.	Product Typ	Size
S0500-00001	Micronel Choke Module MCM-33/10	60 x 50 x 13 mm

Suitable for the motor drivers	Micronel Motor Driver Box MDB-48/10	H023B-048ZX-0
	Micronel Motor Driver Module MDM-48/10	H013B-048ZX-0
Recommended for the blowers	Micronel Radial Blower	U65HN-024KS-6
		U71HN-024KX-6

Micronel Thread Adapter G $\frac{3}{4}$

Connection adapter with two male threads



The brass double nipple is the connecting piece between the blower and vacuum filter. Manufactured with two male threads G $\frac{3}{4}$ to G $\frac{3}{4}$, direct assembly of the accessories is possible.



PROPERTIES

- Bypass adapter with screw-in thread
- Manufactured from rust-free brass

ORDER SPECIFICATION

Article No.	Product Typ	Size
S5200-00001	Micronel Thread Adapter G $\frac{3}{4}$	27 x 28 mm

Suitable blowers for the application	Micronel Radial Blower	U100HL-024KA-4 U100UL-024KA-4 U100H4-024KA-4
--------------------------------------	------------------------	--

Micronel Outlet Port U97XX-009C3

Port to extend outlet



The outlet port can be used to extend the outlet opening on the blower. The port, made of plastics, must be placed over the blower outlet.



PROPERTIES

- Outlet extension
- Made from plastics
- Simple and quick assembly

ORDER SPECIFICATION

Article No.	Product Typ	Size
U97XX-009C3	Micronel Outlet Port U97XX-009C3	Ø 38 mm, 56 x 46 mm

Suitable blowers for the application	Micronel Radial Blower	U97DR-012KK-4 U97DR-024KK-4 U97EM-012KK-3 U97EM-024KK-3 U97EQ-012KK-4 U97EQ-024KK-4 U97HL-024KM-4 U97HL-024KK-4 U97LM-005KK-1
--------------------------------------	------------------------	---

Micronel Outlet Port U97XX-048A3

Port to extend outlet



The outlet port can be used to extend the outlet opening on the blower. The port, made of plastics, must be placed over the blower outlet.



PROPERTIES

- Outlet extension
- Made from plastics
- Simple and quick assembly

ORDER SPECIFICATION

Article No.	Product Typ	Size
U97XX-048A3	Micronel Outlet Port U97XX-048A3	Ø 25 mm, 56 x 37 mm
Suitable blowers for the application	Micronel Radial Blower	U97DR-012KK-4
		U97DR-024KK-4
		U97EM-012KK-3
		U97EM-024KK-3
		U97EQ-012KK-4
		U97EQ-024KK-4
		U97HL-024KM-4
		U97HL-024KK-4
		U97LM-005KK-1

Micronel Inlet Port U97XX-500A9

Port to extend intlet



The inlet port can be used to extend the inlet opening on the blower. The port, made of plastics, must be placed over the blower inlet.



PROPERTIES

- Inlet extension
- Firm hold, inlet extension is screwed to the blower

ORDER SPECIFICATION

Article No.	Product Typ	Size
U97XX-500A9	Micronel Inlet Port U97XX-500A9	Ø 38 mm, 56 x 30 mm
Suitable blowers for the application	Micronel Radial Blower	U97DR-012KK-4
		U97DR-024KK-4
		U97EM-012KK-3
		U97EM-024KK-3
		U97EQ-012KK-4
		U97EQ-024KK-4
		U97HL-024KM-4
		U97HL-024KK-4
		U97LM-005KK-1

**All data are subject to change without advanced notice.
© 2022 by Micronel AG. All rights reserved.**

Micronel AG

Zürcherstrasse 51
CH-8317 Tagelswangen
Phone +41 52 355 16 16
info@micronel.com
www.micronel.com