6-50 WELDER ADAPTERS & CORD SETS

Rating	Pin Conf./NEMA	Source	Compact Adapter	Flexible Adapter	Cord Sets
20A	250V	L6-20P	Industrial Locking	WDL620650	WDL620650 -018	Part # Length (FT.) L620PR (Available in lengths of 10, 25, 50, 75, and 100 feet.)
	125/ 250V	L14-20P	Generator 20 Amp 4-Prong Locking	WDL1420650	WDL1420650 -018	L1420PR (Available in lengths of 10, 25, 50, 75, and 100 feet.)
	3-Phase 250V	L15-20P	Industrial	WDL1520650	WDL1520650 -018	L1520PR (Available in lengths of 10, 25, 50, 75, and 100 feet.)
30A	125V	L5-30P	Generator 30 Amp 3-Prong Locking	WDL530650	WDL530650 -018	Part # Length (FT.) L530PR (Available in lengths of 10, 25, 50, 75, and 100 feet.)
		TT-30P	RV Park	WDTT650	WDTT650 -018	TT30PR (Available in lengths of 10, 25, 50, 75, and 100 feet.)
	250V	6-30P	Commercial HVAC	WD630650	WD630650 -018	N/A
		L6-30P	Industrial Locking	WDL630650	WDL630650 -018	L630PR (Available in lengths of 10, 25, 50, 75, and 100 feet.)
		10-30P	Old Dryer 3-Prong	WD1030650	WD1030650 -018	1030PR (Available in lengths of 10, 25, and 50 feet.)
	125/ 250V	14-30P	New Dryer 4-Prong	WD1430650	WD1430650 -018	1430PR (Available in lengths of 10, 25, and 50 feet.)
		L14-30P	Generator 30A 4-Prong Locking	WDL1430650	WDL1430650 -018	L1430PR (Available in lengths of 10, 25, 50, 75, and 100 feet.)
	3-Phase 250V	L15-30P	Inudstrial	WDL1530650	WDL1530650-018	L1530PR (Available in lengths of 10, 25, 50, 75, and 100 feet.)

NEED HELP?

24/7 Customer Service (414) 434-2220
Text Questions to (414) 323-3240
Email: Info@ACConnectors.com
To Purchase: www.ACWORKS.com
Version 10, ©2018 Cordtec Power Corp.

AC WORKS®

Rating	Pin Conf./NEMA	Source	Compact Adapter	Flexible Adapter	Cord Sets

50A 125/250V

14-50P — RV/EV Range Generator

WD1450650

WD1450650-018

Part # Length (FT.)
1450PR
(Available in lengths of 15, 25, and 50 feet.)

SS2-50P — Common Shore Dock Power

N/A

N/A

WDSS2650-018

TESS2PR
(Available in lengths of 10, 25, 50, 75, and 100 feet.)

WELDER OUTLET ADAPTERS AND EXTENSION CORDS

NEMA 6-50R
50 Amp
250 Volt



WD650PR-010
WD650PR-025
WD650PR-050

50 Amp 250 Volt
Extension Cord

Converting to NEMA	Compact Adapter	Flexible Adapter	Specialty

NEMA 6-20R 20 Amp 250 Volt	**AD650620** 15/20A 250V HVAC Outlet	**S650CB620** 20A 6-15/20 HVAC Outlet with Breaker	**S650W620-018** Three 20A 250V T-Blade Outlets
NEMA 6-30R 30 Amp 250 Volt	**AD650630** 30A 250V HVAC Outlet	**S650630-018** 30A 250V HVAC Outlet	
NEMA L6-20R 20 Amp 250 Volt	**N/A**	**S650L620-018** 20A 250V Locking Outlet	
NEMA L6-30R 30 Amp 250 Volt	**AD650L630** 30A 250V Locking Outlet	**S650L630-018** 30A 250V Locking Outlet	
NEMA 10-30R 30 Amp 250 Volt	**AD6501030** 30A 125/250V Dryer Outlet	**S6501030-018** 30A 125/250V Dryer Outlet	
NEMA 10-50R 50 Amp 250 Volt	**WD6501050** 50A 125/250V Dryer/Range Outlet	**N/A**	
NEMA 14-50R 50 Amp 125/250 Volt	**EV650MS** Tesla EV Charger	**EV650MS-018** Tesla EV Charger	

INTRODUCING PDU OUTLET BOX

- **GFCI Outlets with Waterproof Covers**
- **20 or 24 Amp Breakers**
- **Strong and Durable Housing with Waterproof Lip**
- **Variety of Options for Every Situation**

NEED HELP?

24/7 Customer Service (414) 434-2220
Text Questions to (414) 323-3240
Email: Info@ACConnectors.com
To Purchase: www.ACWORKS.com
Version 10, ©2018 Cordtec Power Corp.

AC WORKS®