


an ISO 9001 company

Fuse Holder, Fuse Clip and Fuse Block Solutions for All Your Needs

Fuse Clips, Fuse Blocks & Fuse Holders





MPD
MEMORY PRACTICE DAILY

MEMORY PROTECTION DEVICES, INC. 200 BROAD HOLLOW RD., SUITE 4, FARMINGDALE, NY 11735, USA

WEBSITE: fuseholders.com E-MAIL: sales@fuseholders.com TEL: +1 631-249-0001 FAX: +1 631-249-0002

INDEX



Fuse Clips and Fuse Holders

2AG and 5mm Fuse Clips

Low-profile, snap-in design, PC retention for wave soldering, available with legs for critical alignment during PC installation, available with or without stops. Rated 6.3 to 30 Amps.



3AG (.250") Fuse Clips and PC Fuse Holders

Low-profile, snap-in design, PC retention for wave soldering, available with legs for critical alignment during PC installation, available with or without stops. Rated 6.3 to 30 Amps.



PC Automotive Blade Fuse Clips

Low-profile, snap-in design, PC retention for wave soldering, available with legs for critical alignment during PC installation, available with or without stops. Rated 6.3 to 30 Amps.



15 Amp PC Automotive Blade Fuse Holders

Thru-hole PC mountable, maintains position during wave soldering. Holder design prevents solder wicking. Shock and vibration resistant. Durable grip, even after multiple uses.



Fuse Clips and Fuse Holders

BK-6001	Snap-in 3AG, PC clip for 1/4" diameter fuse
BK-6002	Snap-in 2AG, PC clip for 5mm diameter fuse
BK-6003	Traditional 3AG, PC clip for 1/4" diameter fuse
BK-6004	3AG, PC fuse holder
BK-6005	Traditional 2AG, PC clip for 5mm diameter fuse
BK-6007	Traditional 3AG, PC clip for 1/4" diameter fuse
BK-6009	PC clip for 5mm diameter fuse

Automotive Blade Fuse Clips

BK-6006	Fuse clip for .205" x .025" standard blade fuses
BK-6008	Fuse clip for .110" x .032" mini blade fuses
BK-6010	Fuse holder for .205" x .025" standard blade fuses
BK-6011	Fuse vertical holder for .10" x .032" mini vertical blade
BK-6012	Fuse clip for .205" x .025" standard blade fuses
BK-6013	Fuse holder for .110" x .032" mini blade fuses

In-line Fuse Holders



In-line Fuse Holders

BF301	In-line fuse holder, add your own 6.35 x 30mm fuses
BF302	In-line fuse holder, 30A-12AWG wire, AGC/ATE/JMC/JTG
BF303	In-line fuse holder, add your own 5 x 20mm fuses
BF309	In-line fuse holder, 30A-14AWG wire, AGC/JMC fuses
BF310	In-line fuse holder, 10A-18AWG wire, AGC/JMC fuses



In-line Fuse Holders





BF301

10A- 12AWG wire
6.3mm x 32mm




BF-302

30A- 12AWG wire
AGC/ATE/JMC/JTG fuses




BF-303

5mm x 20mm
10A GMA/GTE fuses



BF-309

30A- 14AWG wire
AGC/JMC fuses



BF-310


10A- 18AWG wire
AGC/JMC fuses



In-line Blade Fuse Holders


Automotive and Marine Fuse Holders

Blade fuse holders are a reliable and cost-effective solution to protect equipment and electrical applications from damage caused by blown circuits. Fuses are an ideal alternative to circuit breakers because of their small size and ability to protect multiple circuits within a small space. MPD has a wide variety of automotive and marine fuse holders that you can choose from.



BF-351

30A- 12AWG wire
water resistant
ATP/ATC/ATO fuses



BF-352

20A- 16AWG wire
ATP/ATC/ATO fuses

In-line Blade Fuse Holders


BF351	30A-12AWG wire- water resistant- ATP/ATC/ATO fuses
BF352	20A-16AWG wire- ATP/ATC/ATO fuses
BF353	30A-16AWG wire- water resistant- ATP/ATC/ATO fuses
BF353L	80A-8AWG wire- water resistant- MAXI/ATX fuses
BF353S	30A-16AWG wire- water resistant- ATM/ASP fuses
BF354	20A-16AWG wire- water resistant- ATP/ATC/ATO fuses
BF355	20A-16AWG wire- ATP/ATC/ATO fuses
BF356	30A-16AWG wire- ATP/ATC/ATO fuses
BF356S	30A-16AWG wire- ATM/ASP fuses




■ **MEMORY PROTECTION DEVICES, INC.** 200 BROAD HOLLOW RD., SUITE 4, FARMINGDALE, NY 11735, USA

WEBSITE: fuseholders.com E-MAIL: sales@fuseholders.com TEL: +1 631-249-0001 FAX: +1 631-249-0002

In-line Blade Fuse Holders




BF-353
30A- 16AWG wire
water resistant
ATP/ATC/ATO fuses




BF-353L
80A- 8AWG wire
water resistant
MAXI/ATX fuses



BF-353S
30A- 16AWG wire
water resistant
ATM/ASP fuses




BF-354
20A- 16AWG wire
water resistant
ATP/ATC/ATO fuses



BF-355
20A- 16AWG wire
ATP/ATC/ATO fuses



BF-356
30A- 16AWG wire
ATP/ATC/ATO fuses



BF-356S
30A- 16AWG wire
ATM/ASP fuses




MEMORY PROTECTION DEVICES, INC. 200 BROAD HOLLOW RD., SUITE 4, FARMINGDALE, NY 11735, USA

WEBSITE: fuseholders.com E-MAIL: sales@fuseholders.com TEL: +1 631-249-0001 FAX: +1 631-249-0002

Fuse Blocks

We offer a line of Fuse Power Taps for a wide range of applications. All our Fuse Power Taps are constructed of high-quality materials for long-lasting durability. Taps are designed in multiple styles for use with glass and standard fuses. Installation of these fuse blocks requires no crimping. All connections are made by heavy duty screw terminals that can accept up to a 12 gauge wire. They are very easy to install, reduces the amount of wiring time required and typically about the size of a pack of cigarettes. The unit is great for experts who want a simple installation and for novices who are electrically challenged. Suitable for a broad range of household, industrial and commercial uses.



All blocks use AGC/ATE or JMC/SBG fuses.

Individual drawings of our products are available online at www.fuseholders.com



MEMORY PROTECTION DEVICES, INC. 200 BROAD HOLLOW RD., SUITE 4, FARMINGDALE, NY 11735, USA

WEBSITE: fuseholders.com E-MAIL: sales@fuseholders.com TEL: +1 631-249-0001 FAX: +1 631-249-0002