



DWFR TUBING

Dual Wall Heat Shrink Tubing

Highly Flame-Retardant, UL VW-1 Rated

KEY FEATURES

- Highly flame-retardant with UL VW-1 flammability rating
- 3:1 and 4:1 shrink ratios provide design versatility
- Moisture-resistant seal
- Withstands mechanical stress for increased product reliability

APPLICATIONS

- Household appliances
- Automotive
- Commercial electronics and communications
- Consumer products
- Industrial equipment

MATERIALS

- Irradiated polyolefin jacket
- Thermoplastic adhesive inner wall

DWFR tubing from TE Connectivity (TE) is a highly flame-retardant, high-shrink ratio, adhesive-lined tubing made from a polyolefin jacket with a thermoplastic adhesive inner wall. It insulates and environmentally seals and protects components and other electrical connections and terminations. DWFR's medium wall thickness provides increased mechanical protection. Its high shrink ratio allows DWFR to cover a variety of substrates with a limited number of tubing sizes. It is suitable for sealing and protection of connector-to-cable transitions and repairing damaged cable jackets. It can also be used to create and seal breakouts in harnesses.

ELECTRICAL

- Provides excellent electrical insulation

MECHANICAL

- Medium wall jacket provides mechanical protection from abrasion and bending
- Adhesive liner bonds to a variety of substrate materials, providing protection from moisture ingress

TEMPERATURE RATING

- Minimum shrink temperature: 60°C [140°F]
- Full recovery temperature: 110°C [256°F]
- Operating temperature: -40°C to 110°C [-40°F to 230°F]

STANDARDS AND SPECIFICATIONS


- Customer drawing: DWFR
- UL 224 VW-1
- UL file E35586
- Submitted for CSA Certification

ORDERING INFORMATION

- Color: Black (-0)
- Standard packaging (-STK): Cut pieces that are 1.2m [4ft] long. Optional special order packaging (-SP): Spool, varying lengths (consult TE for details)
- Ordering description: Specify product name, size, color and packaging. For example, DWFR-3/1-0-STK

DWFR Tubing

Dual Wall Highly Flame-Retardant Heat Shrink Tubing



DIMENSIONS

Shrink Ratio	Size	Minimum Expanded I.D. (D)	Maximum Recovered I.D. (d)	Total Recovered Wall Thickness (W)	Minimum Recovered Inner Melttable Wall Thickness (W1)
3:1	3/1	3.0 [0.118]	1.0 [0.039]	1.12 ± 0.25 [0.044 ± 0.010]	0.25 [0.010]
	6/2	6.0 [0.236]	2.0 [0.079]	1.14 ± 0.25 [0.045 ± 0.010]	0.25 [0.010]
	9/3	9.0 [0.354]	3.0 [0.118]	1.40 ± 0.25 [0.055 ± 0.010]	0.56 [0.022]
	12/4	12.0 [0.472]	4.0 [0.157]	1.78 ± 0.36 [0.070 ± 0.014]	0.58 [0.023]
	19/6	19.0 [0.748]	6.0 [0.236]	2.25 ± 0.50 [0.088 ± 0.020]	0.58 [0.023]
	24/8	24.0 [0.945]	8.0 [0.315]	2.54 ± 0.50 [0.100 ± 0.020]	0.79 [0.031]
	40/13	40.0 [1.575]	13.0 [0.512]	2.54 ± 0.50 [0.100 ± 0.020]	0.86 [0.034]
4:1	4/1	4.0 [0.157]	1.0 [0.039]	1.12 ± 0.25 [0.044 ± 0.010]	0.25 [0.010]
	8/2	8.0 [0.315]	2.0 [0.079]	1.14 ± 0.25 [0.045 ± 0.010]	0.25 [0.010]
	12/3	12.0 [0.472]	3.0 [0.118]	1.40 ± 0.25 [0.055 ± 0.010]	0.56 [0.022]
	16/4	16.0 [0.630]	4.0 [0.157]	1.78 ± 0.36 [0.070 ± 0.014]	0.58 [0.023]
	24/6	24.0 [0.945]	6.0 [0.236]	2.25 ± 0.50 [0.088 ± 0.020]	0.58 [0.023]
	32/8	32.0 [1.260]	8.0 [0.315]	2.54 ± 0.50 [0.100 ± 0.020]	0.79 [0.031]
	52/13	52.0 [2.047]	13.0 [0.512]	2.54 ± 0.50 [0.100 ± 0.020]	0.86 [0.034]

PRODUCT DESCRIPTION AND ORDERING INFORMATION

Shrink Ratio	Material Description	Material Number
3:1	DWFR-3/1-O-STK	EH2288-000
	DWFR-6/2-O-STK	EH2289-000
	DWFR-9/3-O-STK	EH2290-000
	DWFR-12/4-O-STK	EH2291-000
	DWFR-19/6-O-STK	EH2292-000
	DWFR-24/8-O-STK	EH2293-000
	DWFR-40/13-O-STK	EH2294-000

Shrink Ratio	Material Description	Material Number
4:1	DWFR-4/1-O-STK	EH2295-000
	DWFR-8/2-O-STK	EH2296-000
	DWFR-12/3-O-STK	EH2297-000
	DWFR-16/4-O-STK	EH2298-000
	DWFR-24/6-O-STK	EH2299-000
	DWFR-32/8-O-STK	EH2300-000
	DWFR-52/13-O-STK	EH2301-000

DWFR-3/1-O-STK

- Stick Packaging (Cut pieces that are 1.2m [4ft] long)
- Color is Black
- Size
- Highly Flame-retardant, Dual Wall Product

PROPERTY REQUIREMENTS

Property	Unit	Requirement	Test Method
Physical			
Dimensions*	mm [in]	As shown in DIMENSIONS table	ASTM D 2671
Longitudinal Change	Percent	0, -15%	ASTM D 2671
Tensile Strength*	psi (MPa)	1500 (10.3) minimum	ASTM D 2671
Ultimate Elongation*	Percent	200 minimum	ASTM D 2671
Secant Modulus (Expanded)	psi (MPa)	2.5×10^4 (172) maximum	ASTM D 882, 2% strain
Cold Bend Test at $-30 \pm 1^\circ\text{C}$ ($-22 \pm 1.8^\circ\text{F}$) for 1 hour	-	No cracking	UL 224, section 5.9
Heat Shock* 4 hours at $250 \pm 1^\circ\text{C}$ ($482 \pm 1.8^\circ\text{F}$)	-	No dripping, flowing or cracking of outer wall	UL 224, section 5.8
Heat Resistance 168 hours at $158 \pm 2^\circ\text{C}$ ($347 \pm 4^\circ\text{F}$) followed by test for Tensile strength Elongation	psi (MPa) Percent	70% of original minimum 100% minimum	UL 224
Sealing Efficiency	-	No openings on reheat	AMS-DTL 23053/4
Electrical			
Dielectric Strength	Volts/mil (V/mm)	300 (11,811) minimum on dual wall specimen	ASTM D 2671
Volume Resistivity	ohm/cm	10^{14} minimum on dual wall specimen	ASTM D 2671
Chemical			
Copper Mirror Corrosion 16 hours at $121 \pm 2^\circ\text{C}$ ($250 \pm 4^\circ\text{F}$)	-	No removal of copper	ASTM D 2671, Procedure A
Copper Contact Corrosion 16 hours at $121 \pm 2^\circ\text{C}$ ($250 \pm 4^\circ\text{F}$)	-	No pitting or blackening of copper	ASTM D 2671, Procedure B
Flammability	-	Pass	UL 224, VW-1
Water Absorption 24 hours at 23°C (73°F)	Percent	0.5 maximum	ASTM D 2671

*Denotes Lot Acceptance Test

DWFR Tubing

Dual Wall Highly Flame-Retardant Heat Shrink Tubing

FOR MORE INFORMATION

Visit www.te.com and enter search term "DWFR" or visit www.te.com/DWFRtubing

TE TECHNICAL SUPPORT CENTER

USA: +1 (800) 522-6752

Canada: +1 (905) 475-6222

Mexico: +52 (0) 55-1106-0800

Latin/S. America +54 (0) 11-4733-2200

Germany: +49 (0) 6251-133-1999

UK: +44 (0) 800-267666

France: +33 (0) 1-3420-8686

Netherlands: +31 (0) 73-6246-999

China: +86 (0) 400-820-6015

te.com

All figures are schematic depictions. In every case, relevant product and application specifications take precedence. TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2017 TE Connectivity Ltd. family of companies All Rights Reserved.

1-1773862-9

06/17 Original