




5G

APPLICATIONS

For Diodes
and Rectifiers



5G: THE WAY TO CONNECT EVERYTHING



5G APPLICATIONS

Diodes and Rectifiers



5G Base Stations

- 5 System Architecture (diagram)
- 6 High Current Density Bridge Rectifiers
- 7 Rectifiers
- 8 Schottky Rectifiers
- 9 Low Voltage Rectifiers
- 10 Small Signal Switching Diodes
- 10 Small Signal Schottky Diodes
- 10 Small Signal Zener Diodes



Repeaters

- 12 5G Repeaters (diagram)
- 13 Rectifiers / Transient Voltage Suppressors
- 14 Transient Voltage Suppressors
- 15 Schottky Rectifiers

www.vishay.com

For technical questions within your region, please contact: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com



5G BASE STATIONS

System Architecture (diagram)

High Current Density Bridge Rectifiers

Rectifiers

Schottky Rectifiers


Low Voltage Rectifiers

Small Signal Switching Diodes

Small Signal Schottky Diodes

Small Signal Zener Diodes



SYSTEM ARCHITECTURE





■ High current density bridge rectifiers in compact packages

- Low V_F and high forward surge current capability
- Improves system power efficiency

		I_F (AV)	V_{RRM}	V_F at 125 °C		I_{FSM} at 8.3 ms	Package
	LVB1560	15 A	600 V	0.73 V	7.5 A	400 A	GSIB-5S
	LVE1560	15 A	600 V	0.71 V	7.5 A	300 A	
	LVB2560	25 A	600 V	0.76 V	12.5 A	550 A	
	LVE2560	25 A	600 V	0.74 V	12.5 A	400 A	
	PB3010	30 A	1000 V	0.97 V	15 A	240 A	isoCink+™
	PB3510	35 A	1000 V	0.90 V	17.5 A	350 A	
	PB4010	40 A	1000 V	0.94 V	20 A	400 A	
	PB5010	45 A	1000 V	0.90 V	22.5 A	450 A	



■ Rectifiers in compact packages for auxiliary functions (snubber, clamp, bootstrap, rectifier, etc.)

- Increased power density for space savings
- Improved recovery for better EMC

		I_F (AV)	V_{RRM}	Package
	VS-1EFU06-M3	1 A	600 V	SMF (DO-219AB)
	VS-2EFU06-M3	2 A	600 V	SMF (DO-219AB)
	VS-3EJU06-M3	3 A	600 V	SlimSMA (DO-221AC)
	VS-6ESH06-M3	6 A	600 V	SMPC (TO-277A)

		I_F (AV)	V_{RRM}	Package
	AU1PK	1 A	800 V	SMP (DO-220AA)
	AU2PK	2 A	800 V	SMPC (TO-277A)
	AU3PK	3 A	800 V	SMPC (TO-277A)
	AU1PM	1 A	1000 V	SMP (DO-220AA)
	AU2PM	2 A	1000 V	SMPC (TO-277A)
	AU3PM	3 A	1000 V	SMPC (TO-277A)



■ Schottky rectifiers in compact packages for sub-power in line cards

- Increased power density for space savings


		I_F (AV)	V_{RRM}	V_F at I_F (Typ.)	Package
	VSKY20401608	2 A	40 V	0.51 V	CLP1608-2L
	MSS2P3	2 A	30 V	0.52 V	MicroSMP (DO-219AD)
	V3FL45	3 A	45 V	0.50 V	SMF (DO-219AB)
	V3PM6	3 A	60 V	0.55 V	SMP (DO-220AA)
	VSSAF5M6	5 A	60 V	0.58 V	SlimSMA (DO-221AC)
	VSS8D5M6	5 A	60 V	0.58 V	SlimSMAW (DO-221AD)
	V8PAM12	8 A	120 V	0.63 V at 4 A	SMPA (DO-221BC)

		I_F (AV)	V_{RRM}	V_F at I_F (Typ.)	Package
	V25PL60	25 A	60 V	0.46 V at 12.5 A	SMPC (TO-220A)
	V40PWM15C	20 A x 2	150 V	0.97 V at 10 A / diode	SlimDPAK (TO-252AE)
	V35PWM12	35 A	120 V	0.72 V at 17.5 A	
	V60DM120C	30 A x 2	120 V	0.68 V at 15 A / diode	SMPD (TO-263AC)
	V35DM120	35 A	120 V	0.73 V at 17.5 A	
	V30K45	30 A	45 V	0.54 V	FlatPAK 5 X 6



■ Low voltage rectifiers for bridgeless and multiphase bridgeless topologies

- Increased power density for space savings, improved efficiency

		I_F (AV)	V_{RRM}	Package
	VS-6EVL06-M3	6 A	600 V	SlimDPAK (TO-252AE)
	VS-8ETL06-M3	8 A	600 V	2L TO-220AC
	VS-8ETL06FP-N3	8 A	600 V	2L TO-220 FullPAK
	VS-8EVL06-M3	8 A	600 V	SlimDPAK (TO-252AE)
	VS-10CDU06HM3	2 x 5 A	600 V	SMPD (TO-263AC)
	VS-15ETL06-M3	15 A	600 V	2L TO-220AC
	VS-15ETL06FP-N3	15 A	600 V	2L TO-220 FullPAK


		I_F (AV)	V_{RRM}	Package
	VS-15EVL06-M3	15 A	600 V	SlimDPAK (TO-252AE)
	VS-16EDU06-M3	16 A	600 V	SMPD (TO-263AC)
	VS-E4TU2006FP-N3	20 A	600 V	2L TO-220 FullPAK
	VS-ETU3006-M3	30 A	600 V	2L TO-220AC
	VS-30CDU06-M3	2 x 15 A	600 V	SMPD (TO-263AC)
	VS-ETU3006FP-M3	30 A	600 V	2L TO-220 FullPAK



■ Small signal switching diodes in a compact package

		I_F (AV)	V_{RRM}	t_{rr}	Package
	BAS16WS	0.25 A	100 V	6 ns	SOD-323

■ Small signal schottky diodes in a compact package

		I_F (AV)	V_{RRM}	t_{rr}	Package
	BAS40	0.25 A	40 V	1 V at 40 mA	SOT-23
	VSKY02400603	0.20 A	40 V	0.475 V at 200 mA	CLP0603

■ Small signal zener diodes in a compact package

		P_d	V_z range (typ.)	Package
	PLZ Series	500 mW	2.0 V to 39 V	MicroSMF (DO-219AC)
	BZX384C Series	200 mW	2.4 V to 75 V	SOD-323
	BZX584C Series	200 mW	2.4 V to 51 V	SOD-523



5G REPEATERS


5G Repeaters (diagram)

Rectifiers / Transient Voltage Suppressors

Transient Voltage Suppressors

Schottky Rectifiers

5G REPEATERS





■ Rectifiers for high di/dt snubbers in compact packages

		I_F (AV)	V_{RRM}	t_{rr}	Package
	<u>VS-1EFU06-M3</u>	1.0 A	600 V	55 ns	SMF (DO-219AB)
	<u>VS-2EFU06-M3</u>	2.0 A	600 V	55 ns	SMF (DO-219AB)
	<u>AU1PK</u>	1.0 A	800 V	75 ns	SMP (DO-220AA)
	<u>AU1PM</u>	1.0 A	1000 V	75 ns	SMP (DO-220AA)

■ 200 W to 600 W TVS for snubbers; low clamping ratios

		P_d	V_{BR} (typ.)	V_{WM}	Package
	<u>P2SMA200A</u>	200 W	190 V to 210 V	171 V	SMA (DO-214AC)
	<u>P2SMA220A</u>		209 V to 231 V	185 V	
	<u>P4SMA180A</u>	400 W	171 V to 189 V	154 V	
	<u>P4SMA220A</u>		209 V to 231 V	185 V	
	<u>P6SMB180A</u>	600 W	171 V to 189 V	154 V	SMB (DO-214AA)
	<u>P6SMB200A</u>		190 V to 210 V	171 V	



■ 1500 W to 5000 W TVS with high power density for lightning protection

		P_d	V_{BR} (typ.)	V_{WM}	Package
	<u>SMPC54AN</u>	1500 W	63.2 V	54 V	SMPC (TO-277A)
	<u>1.5SMC91CA</u>		91 V	70.1 V	SMC (DO-214AB)
	<u>SMCJ75CA</u>		87.7 V	75 V	
	<u>SMC3K54CA</u>	3000 W	63.2 V	54 V	
	<u>SMC3K70CA</u>		81.9 V	70 V	
	<u>SMC3K75CA</u>		87.7 V	75 V	
	<u>SMC5K54A</u>	5000 W	63.2 V	54 V	
	<u>SMC5K78A</u>		91.3 V	78 V	

■ 1500 W / 3000 W TVS with high power density for DC/DC protection

		P_d	V_{BR} (typ.)	V_{WM}	Package
	<u>SMCJ15A</u>	1500 W	17.6 V	15 V	SMC (DO-214AB)
	<u>SMCJ24CA</u>		28.1 V	24 V	
	<u>SMCJ33CA</u>		38.7 V	33 V	
	<u>SMCJ36A</u>		42.1 V	36 V	
	<u>1.5SMC39A</u>		39 V	33.3 V	
	<u>TPC24CA</u>		24 V	20.5 V	SMPC (TO-277A)
	<u>TPC36CA</u>		36 V	30.8 V	
	<u>SMC3K24CA</u>	3000 W	28.1 V	24 V	SMC (DO-214AB)



■ Schottky rectifiers in compact packages for auxiliary service and synchronous parallel rectification

		I_F (AV)	V_{RRM}	V_F at I_F (typ.)	Package
	<u>V1FM10</u>	1 A	100 V	0.69 V	SMF (DO-219AB)
	<u>VSKY20401608</u>	2 A	40 V	0.51 V	CLP1608-2L
	<u>V2FM10</u>	2 A	100 V	0.75 V	SMF (DO-219AB)
	<u>MSS2P3</u>	2 A	30 V	0.52 V	MicroSMP (DO-219AD)
	<u>V3FL45</u>	3 A	45 V	0.50 V	SMF (DO-219AB)
	<u>V3PM10</u>	3 A	100 V	0.55 V	SMP (DO-220AA)
	<u>VSSAF5M6</u>	5 A	60 V	0.58 V	SlimSMA (DO-221AC)
	<u>VSS8D5M6</u>	5 A	60 V	0.58 V	SlimSMAW (DO-221AD)

		I_F (AV)	V_{RRM}	V_F at I_F (typ.)	Package
	<u>V8PAM12</u>	8 A	120 V	0.63 V at 4 A	SMPA (DO-221BC)
	<u>V20DM120-M3</u>	20 A	120 V	0.77 V at 10 A	SMPD (TO-263AC)
	<u>V25PL60</u>	25 A	60 V	0.46 V at 12.5 A	SMPC (TO-220A)
	<u>V40PWM15C</u>	20 A x 2	150 V	0.97 V at 10 A / diode	SlimDPAK (TO-252AE)
	<u>V35PWM12</u>	35 A	120 V	0.72 V at 17.5 A	
	<u>V60DM120C</u>	30 A x 2	120 V	0.68 V at 15 A / diode	SMPD (TO-263AC)
	<u>V35DM120</u>	35 A	120 V	0.73 V at 17.5 A	
	<u>V30K45</u>	30 A	45 V	0.54 V	FlatPAK 5 X 6