

LINIER® FULL SIZE SERVER CABINETS

36" Depth



Convex Door/Vented Door
3110-3-001-42

MORE FEATURES/ AFFORDABLE PRICE

LINIER Cabinets are well-respected for their array of features, versatility, security and affordable price.

- 1,300 lb. weight capacity (800 lbs. on casters)
- Preinstalled casters and levelers
- Includes two sets of cage nut style mounting rails
- Removable locking side panels
- Removable slots for cable routing
- Top includes removable laser knockouts to install fans
- 19" EIA 310-D compliant



Easy Installation - Casters and levelers are preinstalled to allow you to easily move and load your system where you need it.


Removable Cable Access Panels - The top and bottom of the server cabinet include removable laser knockouts for cable access and added versatility.

Locking, Removable Side Panels - The side panels are both removable and lockable giving you even better access to your equipment. (Not applicable to 3170)

Adjustable Rails - Includes two sets of adjustable, vertical rails which extend to a maximum depth of 36" for versatile mounting options.

Secured System - Both doors are equipped with locks to protect and secure your valuable equipment. (Feature not applicable to 3170 and 3180 series)

FOUR DOOR TYPES



Also available without doors and/or without side panels

LINIER® FULL SIZE SERVER CABINETS

36" Depth

Door/Series	Size	Dimensions	SKU
3100 Series: Glass Door/ Vented Door	22U	24" W x 37.72" D x 45.50" H	3100-3-001-22
	27U	24" W x 37.72" D x 54.25" H	3100-3-001-27
	37U	24" W x 37.72" D x 71.75" H	3100-3-001-37
	42U	24" W x 37.72" D x 80.50" H	3100-3-001-42
3101 Series: Glass Door/ Solid Door	22U	24" W x 37.72" D x 45.50" H	3101-3-001-22
	27U	24" W x 37.72" D x 54.25" H	3101-3-001-27
	37U	24" W x 37.72" D x 71.75" H	3101-3-001-37
	42U	24" W x 37.72" D x 80.50" H	3101-3-001-42
3102 Series: Convex Door/ Glass Door	22U	24" W x 38.22" D x 45.50" H	3102-3-001-22
	27U	24" W x 38.22" D x 54.25" H	3102-3-001-27
	37U	24" W x 38.22" D x 71.75" H	3102-3-001-37
	42U	24" W x 38.22" D x 80.50" H	3102-3-001-42
3103 Series: Glass Door/ Glass Door	22U	24" W x 37.72" D x 45.50" H	3103-3-001-22
	27U	24" W x 37.72" D x 54.25" H	3103-3-001-27
	37U	24" W x 37.72" D x 71.75" H	3103-3-001-37
	42U	24" W x 37.72" D x 80.50" H	3103-3-001-42
3104 Series: Solid Door/ Convex Door	22U	24" W x 38.22" D x 45.50" H	3104-3-001-22
	27U	24" W x 38.22" D x 54.25" H	3104-3-001-27
	37U	24" W x 38.22" D x 71.75" H	3104-3-001-37
	42U	24" W x 38.22" D x 80.50" H	3104-3-001-42
3105 Series: Convex Door/ Convex Door	22U	24" W x 38.72" D x 45.50" H	3105-3-001-22
	27U	24" W x 38.72" D x 54.25" H	3105-3-001-27
	37U	24" W x 38.72" D x 71.75" H	3105-3-001-37
	42U	24" W x 38.72" D x 80.50" H	3105-3-001-42
3106 Series: Solid Door/ Vented Door	22U	24" W x 37.72" D x 45.50" H	3106-3-001-22
	27U	24" W x 37.72" D x 54.25" H	3106-3-001-27
	37U	24" W x 37.72" D x 71.75" H	3106-3-001-37
	42U	24" W x 37.72" D x 80.50" H	3106-3-001-42
3107 Series: Vented Door/ Vented Door	22U	24" W x 37.72" D x 45.50" H	3107-3-001-22
	27U	24" W x 37.72" D x 54.25" H	3107-3-001-27
	37U	24" W x 37.72" D x 71.75" H	3107-3-001-37
	42U	24" W x 37.72" D x 80.50" H	3107-3-001-42
3108 Series: Solid Door/ Solid Door	22U	24" W x 37.72" D x 45.50" H	3108-3-001-22
	27U	24" W x 37.72" D x 54.25" H	3108-3-001-27
	37U	24" W x 37.72" D x 71.75" H	3108-3-001-37
	42U	24" W x 37.72" D x 80.50" H	3108-3-001-42
3110 Series: Convex Door/ Vented Door	22U	24" W x 38.22" D x 45.50" H	3110-3-001-22
	27U	24" W x 38.22" D x 54.25" H	3110-3-001-27
	37U	24" W x 38.22" D x 71.75" H	3110-3-001-37
	42U	24" W x 38.22" D x 80.50" H	3110-3-001-42
3170 Series: No Doors/ No Side Panels	22U	24" W x 37.72" D x 45.50" H	3170-3-001-22
	27U	24" W x 37.72" D x 54.25" H	3170-3-001-27
	37U	24" W x 37.72" D x 71.75" H	3170-3-001-37
	42U	24" W x 37.72" D x 80.50" H	3170-3-001-42
3180 Series: No Doors	22U	24" W x 37.72" D x 45.50" H	3180-3-001-22
	27U	24" W x 37.72" D x 54.25" H	3180-3-001-27
	37U	24" W x 37.72" D x 71.75" H	3180-3-001-37
	42U	24" W x 37.72" D x 80.50" H	3180-3-001-42

The LINIER® 36" deep cabinets are suitable for network servers, battery backups, switching banks, and other larger pieces of equipment.



Side view with no side panels
3170-3-001-27



LINIER® FIXED WALL MOUNT CABINETS

Stability and durability for your valuable server and network equipment




DIVERSE DOOR OPTIONS


Kendall Howard offers 3 different door styles to accommodate your server and network needs. Each door style can be removed or reversed to be left or right mounted.



GLASS



SOLID



VENTED

ADAPTABLE RAILS

LINIER® fixed wall mount cabinets include one set of adjustable cage nut style rails. For those that prefer a different mounting solution, 10-32 tapped rails are also available.

FEATURES

- Locking side panels
- 250 lb. weight capacity
- 24 rack screws and 24 cage nuts included
- One set of cage nut style mounting rails
- Mounting depth: 22.50"
- 19" EIA compliant
- Made in the USA
- 5-Year Limited Warranty



Hardware
Included


SPECIFICATIONS

SIZE	GLASS DOOR	SOLID DOOR	VENTED DOOR
6U	3140-3-001-06	3141-3-001-06	3142-3-001-06
9U	3140-3-001-09	3141-3-001-09	3142-3-001-09
12U	3140-3-001-12	3141-3-001-12	3142-3-001-12
15U	3140-3-001-15	3141-3-001-15	3142-3-001-15
18U	3140-3-001-18	3141-3-001-18	3142-3-001-18
22U	3140-3-001-22	3141-3-001-22	3142-3-001-22

Call 651.213.1333 or email Sales@kendallhoward.com for pricing and availability

LINIER® SWING OUT WALL MOUNT CABINETS

Cable management and installation made easy with a turn of a key



SWING DESIGN


LINIER® swing out wall mount cabinets allows you to unlock and swing out the cabinet 90 degrees, while hinged to its sturdy back frame mounted to the wall. This creates an additional workspace and permits easy accessibility for terminating, installing and managing cables.

DIVERSE DOOR OPTIONS


Kendall Howard offers 3 different door styles to accommodate your server and network needs. Each door style can be removed or reversed to be left or right mounted.



GLASS



SOLID



VENTED

FEATURES

- 90 degree swing-out
- 150 lb. weight capacity
- Locking side panels
- 24 rack screws and 24 cage nuts included
- One set of cage nut style mounting rails
- Mounting depth: 22.50"
- 19" EIA compliant
- Made in the USA
- 5-Year Limited Warranty



Hardware
Included

SPECIFICATIONS

SIZE	GLASS DOOR	SOLID DOOR	VENTED DOOR
6U	3130-3-001-06	3131-3-001-06	3132-3-001-06
9U	3130-3-001-09	3131-3-001-09	3132-3-001-09
12U	3130-3-001-12	3131-3-001-12	3132-3-001-12
15U	3130-3-001-15	3131-3-001-15	3132-3-001-15
18U	3130-3-001-18	3131-3-001-18	3132-3-001-18
22U	3130-3-001-22	3131-3-001-22	3132-3-001-22

Call 651.213.1333 or email Sales@kendallhoward.com for pricing and availability

12U CORNER WALL MOUNT CABINET

Rethinking your room's workflow possibilities with one visionary design.



12U CORNER WALL MOUNT CABINET
Item #:1915-3-700-12

DESIGNED TO CONFIGURE WITH EASE

The open back design and, top and bottom laser knockouts allow cables to easily be fed into the cabinet. The laser knockouts are also designed for the installation of cooling fans.



CORNER MOUNT DESIGN

Kendall Howard's patented corner design merges our cabinet into the environment saving space, opening walkways, and improving the overall flow of the room.


REMOVABLE LOCKING ACCESS PANELS

Maintenance and changes made easy with removable access panels reveals ample space to manage your rack-mountable equipment.



SIMPLE TO INSTALL

The Phantom Class™ Corner Wall Mount Cabinet is designed and engineered to be installed by one person while still maintaining it's 650 lb load capacity.



FEATURES

- 650 lb. load capacity
- 17.5" usable depth, 27" actual depth
- Adjustable 10-32 tapped rails
- Smoked acrylic front door
- 19" EIA compliant
- Limited Lifetime Warranty
- Made in the USA
- Patent 8,894,161; US D672,342


Call 651.213.1333 or email Sales@kendallhoward.com for pricing and availability

PHANTOM CLASS® OPEN FRAME SWING OUT RACKS

90 degrees and a cutting edge design allows for easy access to install, maintain and improve your rack technology

ONE OF A KIND DESIGN

The Phantom Class® Open Frame Swing-Out Rack is truly in a class of its own. The unrivaled quality allows you to install rackmount equipment up off the floor and easily supports up to 150 lbs. with a 20" usable depth. The 90 degree swing-out provides installers the access to install, manage patch panels, routers, hubs, switches, cabling and other network devices.



12U SWING OUT
Item #1915-3-800-12

18U SWING OUT
Item #:1915-3-800-18



OPEN RACK DESIGN



90 SWING OUT DEGREE ANGLE

FEATURES

- One set of 10-32 tapped rails
- 150 lb. weight capacity
- 20" usable mounting depth
- 19" EIA compliant
- Ships knocked down
- Limited Lifetime Warranty
- Made in the USA



SIMPLE TO INSTALL


Knockdown design reduces shipping charges and backless construction makes assembly a snap. With just a few steps, the rack is easy to assemble with the 16" on center mounting holes that can mount directly to your wall studs.



Call 651.213.1333 or email Sales@kendallhoward.com for pricing and availability

PERFORMANCE PLUS HEAVY DUTY WORKBENCHES

Strength and durability in a modular solution that changes with your needs



SIDE FRAME KITS



Tough modular steel frames allows you to adjust shelves and accessories in 1" increments. The side frames are gangable - modular, allowing you to make your work area perfect for you.

Side Frame Kits	7000-3-001-00
Corner Frame Kit	7000-3-002-00

CORNER WORK SURFACE/SHELF



The corner surface and shelves are 1.25" thick with high density laminate. Each corner surface supports 850 lbs and occupies 4' x 4' area

Corner 24" Shelf Kit	7000-3-0CR-24
Corner 30" Shelf Kit	7000-3-0CR-30

SHELF SUPPORT KITS



One set of steele brackets required for each shelf and work surface.

Shelf Support Kits	7000-1-100-00
--------------------	---------------

WORK SURFACE/SHELF



The work surface and shelves are 1.25" thick with high density laminate. Each work surface supports 850 lbs and are available in 36", 48", 60" and 72", with a 24" and 30" depth option.

BACK PLATES



These heavy-duty back platers are required for each shelf and work surface and also offers cable management

36" Back Plate Kit	7000-1-036-00
48" Back Plate Kit	7000-1-048-00
60" Back Plate Kit	7000-1-060-00
72" Back Plate Kit	7000-1-072-00
Corner Back Plate Kit	7000-1-0CR-00

36" x 24" Shelf Kit	7000-3-036-24
36" x 30" Shelf Kit	7000-3-036-30
48" x 24" Shelf Kit	7000-3-048-24
48" x 30" Shelf Kit	7000-3-048-30
60" x 24" Shelf Kit	7000-3-060-24
60" x 30" Shelf Kit	7000-3-060-30
72" x 24" Shelf Kit	7000-3-072-24
72" x 30" Shelf Kit	7000-3-072-30

Call 651.213.1333 or email Sales@kendallhoward.com for pricing and availability

PERFORMANCE SERIES® WORKBENCHES

Kendall Howard builds quality multipurpose workspaces that work as hard as you



**casters not included*

MODULAR SOLUTIONS

The Performance Series design allows your workspace to evolve with the workload. Available in 24", 48", 72" and 96" lengths and 5 different models which allows you to create the configuration that best suits your environment.

FEATURES

- Assembles in less than 30 minutes
- Completely modular design
- Adjust upper shelving in any increment
- 1,000 lb. weight capacity
- Various sizes available: 24", 48", 72" and 96"
- Built in cable management
- Accessories available
- Choose one of 2 stunning Melamene finishes
- Made in the USA
- Limited Lifetime Warranty



SERIES 100

- Adjustable upper shelves
- 14" depth bottom shelf

SERIES 200

- Adjustable upper shelves
- 28" depth bottom shelf



SERIES 300

- Work surface and bottom shelf
- 14" depth bottom shelf



SERIES 400


- Work surface and bottom shelf
- 28" depth bottom shelf



CORNER SERIES

- Modular design
- Adjustable upper shelves

SURFACE **shades may differ*



FOLKSTONE



AFRICAN
MAHOGANY

Call 651.213.1333 or email Sales@kendallhoward.com for pricing and availability

PERFORMANCE SERIES® WORKBENCHES



FOLKSTONE

**actual color shades may vary*

SERIES	24 Inch	48 Inch	72 Inch	96 Inch
SERIES 100	5000-3-100-24	5000-3-100-48	5000-3-100-72	5000-3-200-96
SERIES 200	5000-3-200-24	5000-3-200-48	5000-3-200-72	5000-3-200-96
SERIES 300	5000-3-300-24	5000-3-300-48	5000-3-300-72	5000-3-300-96
SERIES 400	5000-3-400-24	5000-3-400-48	5000-3-400-72	5000-3-400-96

CORNER SERIES	5000-3-100-CR
---------------	---------------



AFRICAN
MAHOGANY

**actual color shades may vary*

SERIES	24 Inch	48 Inch	72 Inch	96 Inch
SERIES 100	5000-3-104-24	5000-3-104-48	5000-3-104-72	5000-3-204-96
SERIES 200	5000-3-204-24	5000-3-204-48	5000-3-204-72	5000-3-204-96
SERIES 300	5000-3-304-24	5000-3-304-48	5000-3-304-72	5000-3-304-96
SERIES 400	5000-3-404-24	5000-3-404-48	5000-3-404-72	5000-3-404-96

CORNER SERIES	5000-3-104-CR
---------------	---------------

The Answer is Yes! What's the Question?

Kendall Howard
10152 Liberty Lane
Chisago City, MN 55013
Phone: 651-213-1333
www.kendallhoward.com

ADVANCED CLASSROOM TRAINING TABLES

A polished learning and workspace accentuated by its accessories

DATA CONVERSION KIT

Item #:5500-3-100-01



TRAINING TABLE CABLE MANAGEMENT ENCLOSURE

36" 5500-3-100-36
48" 5500-3-100-48
60" 5500-3-100-60
72" 5500-3-100-72



CPU HOLDER

Standard #:5500-3-100-01
SFF #:5500-3-100-04



ACRYLIC COUGH & SNEEZE BARRIER

Custom sizes available
Contact us for more information



TRAINING TABLE KEYBOARD TRAY

Item #:5500-3-100-02



LOCKING CASTER KIT

Item #:5500-3-100-03



SURFACES

**shades may differ*



FOLKSTONE



AFRICAN
MAHOGANY

EASY TO ASSEMBLE

The Kendall Howard Advanced Classroom Training Table Collection balances professionalism and practicality in a truly universal solution. The ACTT system will easily convert an outdated, uninspiring training room into an engaging, respectable atmosphere by providing a clean, focused learning space that is suitable for any training or work space.

- 350 lb. weight capacity
- Made in the USA
- Limited Lifetime Warranty
- Available for single and dual use
- Leg kit - Black powder coat
- Surface melamine



Ships Freight



Assembly
Required

Call 651.213.1333 or email Sales@kendallhoward.com for pricing and availability

ADVANCED CLASSROOM TRAINING TABLE

EASY TO ASSEMBLE

Whether assembling a single table or a whole classroom, installation is quick and easy with the use of standard hardware and tools. Durable surface features pre-drilled holes for the base and all accessories; only requiring a Philips head screwdriver to complete the job..

QUALITY CONSTRUCTION

Uncompromising leg construction and robust table tops offer a solid, durable solution that can withstand years of use, and multiple relocations.

VARIOUS DEPTHS AND WIDTHS

We know training facilities vary in size. That is why we offer two depths (24"/30") and four lengths (36"/48"/60"/72") to suit applications in oversized and tight locations.

SURFACE	36"W x 24"D	48"W x 24"D	60"W x 24"D	72"W x 24"D
Folkstone	5500-3-000-23	5500-3-000-24	5500-3-000-25	5500-3-000-26
African Mahogany	5500-3-004-23	5500-3-004-24	5500-3-004-25	5500-3-004-26

SURFACE	36"W x 30"D	48"W x 30"D	60"W x 30"D	72"W x 24"D
Folkstone	5500-3-000-33	5500-3-000-34	5500-3-000-35	5500-3-000-36
African Mahogany	5500-3-004-33	5500-3-004-34	5500-3-004-35	5500-3-004-36

The Answer is Yes! What's the Question?

Kendall Howard
10152 Liberty Lane
Chisago City, MN 55013
Phone: 651-213-1333
www.kendallhoward.com

KENDALL HOWARD

ESD TECHNICAL FURNITURE

Kendall Howard's ESD products offer simplicity and static protection never seen before!

ESD MADE EASY

Engineered for optimal ergonomics and static control, the ESD furniture series is the solution for professionals in static control environments. Create an ideal ESD safe work space for servicing and maintenance of sensitive electronic components.



MOBILE ESD CART

Introducing an industry first Variable Height ESD Cart! This cart features an electronically controlled work surface allowing height adjustability from 29" to 54". Lithium-Ion battery and intelligent controllers allow for pre-programmable height settings to quickly recall desired heights.

US Patent: 10,881,040

Item #:ESD-EVH-1000



ESD CABINET

Designed with versatility and protection in mind. Our fully enclosed cabinet is equipped with locking split-entry doors to ensure sensitive equipment is safe. The cabinet is complete with a fully integrated louvered panel system featuring 153 louvered cut outs for mounting additional accessories.

ESD Core Cabinet

Item #:ESDC-7836-1000

ESD Cabinet with Accessories

Item #:ESDC-7836-2000



ESD WORKBENCH

The Kendall Howard ESD Workbench series brings static controlled furniture in to a category of its own. With the ability to adjust the work surface height from 30"-38", adjusting to user needs has never been easier. The conductive work surface provides protection from static charges and is resistant to most solvents & solders.

48" ESD Workbench: Item #:ESDW-4830-1000

60" ESD Workbench: Item #:ESDW-6030-1000

96" ESD Workbench: Item #:ESDW-9630-1000

Call 651.213.1333 or email sales@kendallhoward.com for pricing and availability