




2773 Series WALL-NUTS®

The Way to Connect - Splicing Connectors with PUSHWIRE® technology




2773 Series WALL-NUTS® PUSHWIRE® Splicing Connectors


It's never been easier! Push your way to fast, reliable connections – no twisting required. The NEW 2773 Series with PUSHWIRE® technology – a modern version of the original WALL-NUTS® is the compact, clear choice for any splicing job.

Your Advantages

- Eliminates wrist and finger strain – no twisting, crimping, or taping required
- Up to 50% faster to terminate wires compared to a twist-type connector
- Compact design – smallest in the industry which reduces box fill
- WALL-NUTS® utilize one stainless steel spring, per conductor, to provide independent contact force against a copper current bar
- Allows for pre-fabrication of conductors making field installation easier
- 2-year warranty




Strip Length Indication



Strip solid or stranded conductor to 13 mm (0.51 inch).

Strip gauge can be found on the side of the connector with the markings.


PUSHWIRE® Technology



Simply push-in the stripped conductor until it hits the backstop. Different conductor types can be combined.

Low insertion forces with high retention forces for a secure connection.

Visual Inspection Window



The visual inspection window ensures a proper termination, every time (✓).


If the conductor is showing in the inspection window, the wire has been stripped incorrectly (✗).

Built-in Test Port



Test port located opposite the conductor entry for easy access.

Conductor Removal



Solid conductor: hold wire and twist left and right while pulling the connector. Approved for reuse.

Stranded conductor: cut the wire, re-strip and insert into a new connector.

Mounting Options



The mounting carrier allows the connectors to be DIN-rail or chassis mounted.



The No-Twist Solution for all of your Termination Projects

2773 Series

Solid: 20 - 12 AWG

Stranded: 16 - 12 AWG (≤19 Strands)

18 AWG-TC (≤7 Strands)



600 V (1000 V signs and fixtures)

20 A





LISTED
Splicing Wire Connector
486C



LISTED
GROUNDING EQUIP
64KA

Continuous service max.
operating temperature:
105 °C / 221 °F

	Description	Item No.		Pieces Per Pack
	2-wire connector	2773-402/K000-0002	Box	120
		2773-402/VE00-2500	Bulk	2,500
		2773-402/VE00-0500	Bulk	500
	3-wire connector	2773-403/K000-0002	Box	100
		2773-403/VE00-2500	Bulk	2,500
		2773-403/VE00-0500	Bulk	500
	4-wire connector	2773-404/K000-0002	Box	80
		2773-404/VE00-2500	Bulk	2,500
		2773-404/VE00-0500	Bulk	500
	5-wire connector	2773-405/K000-0002	Box	60
		2773-405/VE00-2500	Bulk	2,500
		2773-405/VE00-0500	Bulk	500
	6-wire connector	2773-406/K000-0002	Box	50
		2773-406/VE00-2500	Bulk	2,500
		2773-406/VE00-0500	Bulk	500
	8-wire connector	2773-408/K000-0002	Box	40
		2773-408/VE00-2500	Bulk	2,500
		2773-408/VE00-0500	Bulk	500
	Mounting Carrier	2773-500	Box	10

Global Approvals



WAGO Corporation

N120 W19129 Freistadt Road
Germantown, Wisconsin 53022
Telephone: 800 / DIN Rail (346-7245)
Fax: 262 / 255-3232
info.us@wago.com
www.wago.us

Canada

WAGO Canada, Inc.
1550 Yorkton Court, Unit 1
Burlington, ON L7P 5B7
Telephone: (888) WAGO-221 (924-6221)
www.wago.ca

Mexico

WAGO Corporation
Queretaro
Tel. 001/800/309/5975
+ 52/442/221/5946
Fax + 52/442/221/5063
www.wago.mx

WAGO is a registered trademark of WAGO Verwaltungsgesellschaft mbH.

"Copyright – WAGO Kontakttechnik GmbH & Co. KG – all rights reserved. The content and structure of the WAGO Websites, catalogs, videos, and other WAGO media are subject to copyright. The dissemination or changing of the content of these pages and videos is not permitted. Furthermore, the content may neither be copied nor made available to third parties for commercial purposes. Also subject to copyright are the images and videos that were made available to WAGO Kontakttechnik GmbH & Co. KG by third parties."