



Infineon AIROC™ Wi-Fi and Bluetooth® IoT partner module selector guide

www.infineon.com



Table of contents

Infinion AIROC™ Wi-Fi and Bluetooth® IoT partner module selector guide (Chapters)

1. Infineon AIROC™ Wi-Fi and Bluetooth® wireless connectivity	3
2. Infineon IoT software solutions	4
3. Wi-Fi 6/6E (802.11ax) + Dual-Mode Bluetooth® combo partner module portfolio	5
4. Wi-Fi 5 (802.11ac) + Dual-Mode Bluetooth® combo partner module portfolio	11
5. Wi-Fi 4 (802.11n) + Dual-Mode Bluetooth® combo partner module portfolio	15
6. Wi-Fi Connected MCU partner module portfolio	18
7. Bluetooth® and Bluetooth® Low Energy (Dual-Mode) partner module portfolio	23

Infineon AIROC™ Wi-Fi and Bluetooth® wireless connectivity

Delivering differentiated capabilities purpose-built for the IoT

Industry's broadest portfolio of Wi-Fi and Wi-Fi + Bluetooth® combo devices



- Infineon has the ideal Wi-Fi solution for any application providing both single- and dual-band 802.11n/ac/ax SISO and MIMO devices
- Infineon provides Wi-Fi + Bluetooth® combo chipsets – integrating our world-class Wi-Fi with powerful Bluetooth®/ Bluetooth® Low Energy to ease onboarding of cloud-connected IoT devices via a mobile app
- Infineon provides AIROC™ Wi-Fi connectivity processors and PSOC™ Bluetooth® MCUs with Bluetooth® Low Energy



Reliable

- More than 1 billion Wi-Fi devices in the field
- High-performance RF architecture provides longer range and better interference rejection



Low power

- Ultra low power – very low sleep, transmit, and receive current
- Continuous improvements to battery life via a unique visibility into real-world power consumption



Secure

- Most widely vetted Wi-Fi / Bluetooth® devices on the market, with security researchers extensively focused on Infineon
- Deep domain knowledge and processes to help customers secure products throughout the lifecycle



Infineon wireless module partner ecosystem

Our global partner ecosystem enables development of IoT applications on time, on budget, and with minimized risk.

- Hardware** – Avoid complicated and costly chip-down designs with a pre-built wireless module providing multiple antenna options and services
- Software** – Take advantage of pre-configured connectivity software for common MPUs, operating systems, and development tools
- Certifications** – Don't worry about multiple global regulatory bodies with full modular and reference-certified RF modules (CE, IC, FCC, etc.)
- Support** – Get to production with partner support and services including antenna and plastics design, EMC testing, and more

muRata
INNOVATOR IN ELECTRONICS

AzureWave

ezurio

u-blox

Inventek Systems
Embedding Connectivity Everywhere

LANTRONIX
CONNECT SMART. DO MORE.

USI

QUECTEL

Build a Smarter World

Infineon IoT software solutions




Infineon provides reliable and consistently updated software development platforms for flexible and rapid development of your connected product.

Solutions for RTOS designs

Infineon delivers compute, connectivity, and HMI capabilities in a single unified platform: The ModusToolbox™ software environment.


- ModusToolbox™ is a set of multi-platform tools and a suite of middleware libraries enabling industry-leading feature-sets like CAPSENSE™ capacitive-sensing, mesh, and system power optimization
- Enables an immersive development experience for Infineon MCU and wireless devices. You can use our Eclipse IDE for ModusToolbox™, or 3rd-party IDEs such as Visual Studio Code, IAR Embedded Workbench, and Keil µVision
- Extensive support for 3rd-party cloud ecosystems including our own cloud management solution using the ultra-low-power AIROC™ Wi-Fi connectivity processors



Solutions for Linux/Android designs

Delivering integrated wireless products for Linux and Android designs. Infineon partners with the open-source community to provide quality and secure connectivity.

- ModusToolbox™ Enabling a broad set of Wi-Fi and Bluetooth®/ Bluetooth® LE advanced feature sets for a wide variety of designs
- Supporting the latest Linux and Android distributions along with backward-compatibility for previous versions
- Infineon RF and regulatory tools bring your Linux- or Android-based prototype to production faster than ever



Wi-Fi 6/6E (802.11ax) + Dual-Mode Bluetooth® combo partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	Dim (xyz-mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW55573	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XB583MA-PUR	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	22 x 30 x 2.06	-40 to +85	Follow AW-XH323's FCC	SMD	M.2 2230	Ext.antenna by MHF4 connectors	PCIe	UART
CYW55573	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XB583MA-SUR	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	22 x 30 x 2.06	-40 to +85	Follow AW-XH323's FCC	SMD	M.2 2230	Ext.antenna by MHF4 connectors	SDIO	UART
CYW55573	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XH323-PUR	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	10 x 10 x 1.26	-40 to +85	AW-XH323-xxx, AW-XH325-xxx and AW-XH327-xxx share the sameFCC	SMD	SiP	RF pad	PCIe	UART
CYW55573	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XH323-SUR	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	10 x 10 x 1.26	-40 to +85	AW-XH323-xxx, AW-XH325-xxx and AW-XH327-xxx share the sameFCC	SMD	SiP	RF pad	SDIO	UART
CYW55573	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XM643-PUR	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	13 x 15 x 1.95	-40 to +85	TBD	SMD	LGA	RF pad	PCIe	UART
CYW55573	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XM643-SUR	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	13 x 15 x 1.95	-40 to +85	TBD	SMD	LGA	RF pad	SDIO	UART
CYW55573	Wi-Fi 6/6E (802.11ax)	Embedded Artists	EAR00413	2.4/5/6 GHz	-	Bluetooth®/ Bluetooth® LE 5.3	-	-	-	M.2 plug-in	E-key 2244	Integrated trace antenna	-	-
CYW55573	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00117C	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 6.0	13 x 18 x 1.9	-40 to +85	FCC,ISED, CE, UKCA, MIC, RCM & Bluetooth® SIG	SMD	M.2 1318 SMT	MHF4 antenna (Cut Tape)	SDIO,PCIe	UART, I²S, PCM
CYW55573	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00117R	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 6.0	13 x 18 x 1.9	-40 to +85	FCC,ISED, CE, UKCA, MIC, RCM & Bluetooth® SIG	SMD	M.2 1318 SMT	MHF4 antenna (Tape & Reel)	SDIO,PCIe	UART, I²S, PCM
CYW55573	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00118C	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 6.0	13 x 18 x 1.9	-40 to +85	FCC,ISED, CE, UKCA, MIC, RCM & Bluetooth® SIG	SMD	M.2 1318 SMT	RF trace an- tenna (Cut Tape)	SDIO,PCIe	UART, I²S, PCM
CYW55573	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00119	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 6.0	22 x 30 x 2.7	-40 to +85	FCC,ISED, CE, UKCA, MIC, RCM & Bluetooth® SIG	M.2 plug-in	E-key 2230	MHF4 antenna (Carton)	SDIO	UART, I²S, PCM
CYW55573	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00119-K1	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 6.0	22 x 30 x 2.7	-40 to +85	FCC,ISED, CE, UKCA, MIC, RCM & Bluetooth® SIG	DVK	E-key 2230	-	SDIO	-
CYW55573	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00120	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 6.0	22 x 30 x 2.7	-40 to +85	FCC,ISED, CE, UKCA, MIC, RCM & Bluetooth® SIG	M.2 plug-in	E-key 2230	MHF4 antenna (Carton)	PCIe	UART, I²S, PCM

Wi-Fi 6/6E (802.11ax) + Dual-Mode Bluetooth® combo partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	Dim (xyz-mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW55573	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00120-K1	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 6.0	22 x 30 x 2.7	-40 to +85	FCC, ISED, CE, UKCA, MIC, RCM & Bluetooth® SIG	DVK	E-key 2230	-	PCIe	-
CYW55573	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00118R	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 6.0	13 x 18 x 1.9	-40 to +85	FCC, ISED, CE, UKCA, MIC, RCM & Bluetooth® SIG	SMD	M.2 1318 SMT	RF Trace antenna (Tape & Reel)	SDIO, PCIe	UART, I²S, PCM
CYW55573	Wi-Fi 6/6E (802.11ax)	Murata	LBEE5 V2EA-802	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	12.5 x 9.4 x 1.2	-40 to +85	FCC/IC/CE/TELEC	SMD	LGA	Dipole ANT, monopole TraceANT	SDIO, PCIe	UART, I²S, PCM
CYW55573	Wi-Fi 6/6E (802.11ax)	USI	WM-CW-61	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 6.1	11 x 11 x 1.2	-40 to +85	N/A	SMD	SIP	N/A	SDIO	UART
CYW55513	Wi-Fi 6/6E (802.11ax)	USI	WM-CW-61M	2.4/5/6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 6.0	15 x 18 x 3	-40 to +85	N/A	SMD	LGA (Metal Shielding on PCB)	IPEX connector	SDIO, PCIe	UART
CYW55513	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XM606	2.4/5/6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	12 x 12 x 1.21	-40 to +85	TBD	SMD	LGA	RF pad	SDIO	UART, PCM
CYW55513	Wi-Fi 6/6E (802.11ax)	Embedded Artists	EAR00511	2.4/5/6 GHz	-	Bluetooth®/ Bluetooth® LE 5.4	-	-	-	M.2 plug-in	E-key 2230	u.fl	-	-
CYW55513	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00184C	2.4/5/6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 6.0	12 x 16 x 1.9	-40 to +85	FCC, ISED, CE, UKCA, MIC, RCM & Bluetooth® SIG	SMD	M.2 1216 SMT	MHF4L antenna (Cut Tape)	SDIO	UART, SDIO, SPI
CYW55513	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00184R	2.4/5/6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 6.0	12 x 16 x 1.9	-40 to +85	FCC, ISED, CE, UKCA, MIC, RCM & Bluetooth® SIG	SMD	M.2 1216 SMT	MHF4L antenna (Tape & Reel)	SDIO	UART, SDIO, SPI
CYW55513	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00185C	2.4/5/6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 6.0	12 x 16 x 1.9	-40 to +85	FCC, ISED, CE, UKCA, MIC, RCM & Bluetooth® SIG	SMD	M.2 1216 SMT	RF Trace antenna (Cut Tape)	SDIO	UART, SDIO, SPI
CYW55513	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00185R	2.4/5/6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 6.0	12 x 16 x 1.9	-40 to +85	FCC, ISED, CE, UKCA, MIC, RCM, Bluetooth® SIG	SMD	M.2 1216 SMT	RF Trace antenna (Tape & Reel)	SDIO	UART, SDIO, SPI
CYW55513	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00186	2.4/5/6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 6.0	22 x 30 x 2.7	-40 to +85	FCC, ISED, CE, UKCA, MIC, RCM, Bluetooth® SIG	M.2 plug-in	E-key 2230	MHF4L antenna (Carton)	SDIO	UART, I²S, PCM
CYW55513	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00186-K1	2.4/5/6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 6.0	22 x 30 x 2.7	-40 to +85	FCC, ISED, CE, UKCA, MIC, RCM & Bluetooth® SIG	DVK	M.2 plug-in	1x MHF4L connector	-	-
CYW55513	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00193C	2.4/5/6 GHz	1T1R (Diversity)	Bluetooth®/ Bluetooth® LE 6.0	12 x 16 x 1.9	-40 to +85	FCC, ISED, CE, UKCA, MIC, RCM & Bluetooth® SIG	SMD	M.2 1216 SMT	2x MHF4L antenna	SDIO	UART, SDIO, SPI

Wi-Fi 6/6E (802.11ax) + Dual-Mode Bluetooth® combo partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	Dim (xyz-mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW55513	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00193R	2.4/5/6 GHz	1T1R (Diversity)	Bluetooth®/ Bluetooth® LE 6.0	12 x 16 x 1.9	-40 to +85	FCC, ISSED, CE, UKCA, MIC, RCM & Bluetooth® SIG	SMD	M.2 1216 SMT	2x MHF4L antenna	SDIO	UART, SDIO, SPI
CYW55513	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00194C	2.4/5/6 GHz	1T1R (Diversity)	Bluetooth®/ Bluetooth® LE 6.0	12 x 16 x 1.9	-40 to +85	FCC, ISSED, CE, UKCA, MIC, RCM & Bluetooth® SIG	SMD	M.2 1216 SMT	2x Trace pin	SDIO	UART, SDIO, SPI
CYW55513	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00194R	2.4/5/6 GHz	1T1R (Diversity)	Bluetooth®/ Bluetooth® LE 6.0	12 x 16 x 1.9	-40 to +85	FCC, ISSED, CE, UKCA, MIC, RCM & Bluetooth® SIG	SMD	M.2 1216 SMT	2x Trace pin	SDIO	UART, SDIO, SPI
CYW55513	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00195	2.4/5/6 GHz	1T1R (Diversity)	Bluetooth®/ Bluetooth® LE 6.0	22 x 30 x 2.7	-40 to +85	FCC, ISSED, CE, UKCA, MIC, RCM & Bluetooth® SIG	M.2 plug-in	E-Key 2230	MHF4 antenna (Carton)	SDIO	UART, I²S, PCM
CYW55513	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00195-K11	2.4/5/6 GHz	1T1R (Diversity)	Bluetooth®/ Bluetooth® LE 6.0	22 x 30 x 2.7	-40 to +85	FCC, ISSED, CE, UKCA, MIC, RCM & Bluetooth® SIG	DVK	E-Key 2230	2x MHF4L Connector (Antenna Diversity)	-	-
CYW55513	Wi-Fi 6/6E (802.11ax)	Murata	LBEE5HY2FY-922	2.4/5/6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	7.9 x 7.3 x 1.1	-40 to +85	FCC/IC/CE/ TELEC(Planning)	SMD	LGA	Dipole ANT, monopole trace ANT(planning)	SDIO	UART, I²S, PCM
CYW55513	Wi-Fi 6/6E (802.11ax)	Quectel	FCS963N-LP	2.4/5/6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	12 X 12 x 1.55	-40 to +85	China (SRRC)/FCC/CE IC/RCM (planning)	SMD	LCC stamp	1 x 1	SDIO, QSPI	UART, PCM
CYW55513	Wi-Fi 6/6E (802.11ax)	u-blox	MAYA-W383	2.4/5/6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	10.4 x 14.3 x 1.9	-40 to +85	FCC, ISSED, CE, UKCA, MIC, & Bluetooth® SIG (in dev)	SMD	LGA	Single antenna pin	SDIO, GSPI	UART, SDIO, SPI
CYW55513	Wi-Fi 6/6E (802.11ax)	u-blox	MAYA-W381	2.4/5/6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	10.4 x 14.3 x 1.9	-40 to +85	FCC, ISSED, CE, UKCA, MIC, & Bluetooth® SIG (in dev)	SMD	LGA	2 antenna pins	SDIO, GSPI	UART, SDIO, SPI
CYW55513	Wi-Fi 6/6E (802.11ax)	u-blox	MAYA-W386	2.4/5/6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	10.4 x 14.3 x 1.9	-40 to +85	FCC, ISSED, CE, UKCA, MIC, & Bluetooth® SIG (in dev)	SMD	LGA	PCB antenna	SDIO, GSPI	UART, SDIO, SPI
CYW55513	Wi-Fi 6/6E (802.11ax)	u-blox	EVK-MAYA-W381	2.4/5/6 GHz	-	Bluetooth®/ Bluetooth® LE 6.0	-	-40 to +85	-	EVK	-	2 antenna pins	-	-
CYW55513	Wi-Fi 6/6E (802.11ax)	u-blox	EVK-MAYA-W386	2.4/5/6 GHz	-	Bluetooth®/ Bluetooth® LE 6.0	-	-40 to +85	-	EVK	-	Embedded antenna	-	-
CYW55513	Wi-Fi 6/6E (802.11ax)	u-blox	M2-MAYA- W383-00C	2.4/5/6 GHz	-	Bluetooth®/ Bluetooth® LE 6.0	22 x 30	-40 to +85	-	M.2	E-key 2230	Single U.FL connector	SDIO, GSPI	UART, SDIO, SPI
CYW55513	Wi-Fi 6/6E (802.11ax)	u-blox	M2-MAYA- W383-10C	2.4/5/6 GHz	-	Bluetooth®/ Bluetooth® LE 6.0	22 x 30	-40 to +85	-	M.2	E-key 2230	Single U.FL connector	SDIO, GSPI	UART, SDIO, SPI

Wi-Fi 6/6E (802.11ax) + Dual-Mode Bluetooth® combo partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	Dim (xyz-mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW55513	Wi-Fi 6/6E (802.11ax)	USI	WM-CW-65	2.4/5/6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 6.1	8.6 x 8.1 x 1.1	-40 to +85	N/A	SMD	LGA (Molding SIP)	N/A	SDIO	UART
CYW55513	Wi-Fi 6/6E (802.11ax)	USI	WM-CW-65M	2.4/5/6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 6.1	8.6 x 8.1 x 1.1	-	N/A	SMD	LGA (Metal Shielding on PCB)	N/A	SDIO	UART
CYW55533	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XM664-SD	2.4/5/6 GHz	1T1R	N/A	12 x 12 x 1.65	-40 to +85	FCC	SMD	LGA	RF pad	SDIO	N/A
CYW55533	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XM664-USB	2.4/5/6 GHz	1T1R	N/A	12 x 12 x 1.65	-40 to +85	FCC	SMD	LGA	RF pad	USB	N/A
CYW55572	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XB327 MA-PUR	2.4/5 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	22 x 30 x 2.06	-40 to +85	Follow AW-XH327's FCC	M.2 plug-in	M.2 2230	Ext. antenna by MHF4 connectors	PCIe	UART
CYW55572	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XB327 MA-SUR	2.4/5 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	22 x 30 x 2.06	-40 to +85	Follow AW-XH327's FCC	M.2 plug-in	M.2 2230	Ext. antenna by MHF4 connectors	SDIO	UART
CYW55572	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XH327-PUR	2.4/5 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	10 x 10 x 1.26	-40 to +85	AW-XH323-xxx, AW-XH325-xxx and AW-XH327 xxx share the same FCC	SMD	SIP	RF pad	PCIe	UART
CYW55572	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XH327-SUR	2.4/5 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	10 x 10 x 1.26	-40 to +85	AW-XH323-xxx, AW-XH325-xxx and AW-XH327 xxx share the same FCC	SMD	SIP	RF pad	SDIO	UART
CYW55572	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XM612-PUR	2.4/5 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	13 x 15 x 1.95	-40 to +85	TBD	SMD	LGA	RF pad	PCIe	UART
CYW55572	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XM612-SUR	2.4/5 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	13 x 15 x 1.95	-40 to +85	TBD	SMD	LGA	RF pad	SDIO	UART
CYW55572	Wi-Fi 6/6E (802.11ax)	Iton	IW5572-50B1	2.4/5 GHz	2T2R	Bluetooth® LE 5.3	15 x 13	-40 to +85	FCC/CE/SRRC ROHS/BQB	SMD	PCB Module	External antenna	SDIO	UART, I²S, PCM
CYW55572	Wi-Fi 6/6E (802.11ax)	USI	WM-CW-51	2.4/5 GHz	2T2R	Bluetooth®/ Bluetooth® LE 6.0	11 x 11 x 1.2	-40 to +85	N/A	SMD	LGA (Molding SIP)	N/A	SDIO	UART
CYW55572	Wi-Fi 6/6E (802.11ax)	USI	WM-CW-51H	2.4/5 GHz	2T2R	Bluetooth®/ Bluetooth® LE 6.0	14.5 x 15 x 1.5	-40 to +85	N/A	SMD	LGA (Molding SIP)	N/A	SDIO	UART

Wi-Fi 6/6E (802.11ax) + Dual-Mode Bluetooth® combo partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	Dim (xyz-mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW55512	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XM650	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	12 x 12 x 1.21	-40 to +85	TBD	SMD	LGA	N/A	SDIO	UART, PCM
CYW55512	Wi-Fi 6/6E (802.11ax)	Murata	LBEE5XV2GY-001	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	7.9 x 7.3 x 1.1	-40 to +85	FCC/IC/CE/ TELEC(Planning)	SMD	LGA	Dipole ANT, monopole Trace ANT(Planning)	SDIO	UART, I²S, PCM
CYW55512	Wi-Fi 6/6E (802.11ax)	Quectel	FCS962N-LP	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	12 x 12 x 1.55	-40 to +85	China (SRRC)/ FCC/CE/IC/RCM (planning)	SMD	LGA	1 x 1	SDIO, QSPI	UART, PCM
CYW55512	Wi-Fi 6/6E (802.11ax)	u-blox	MAYA-W363	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	10.4 x 14.3 x 1.9	-40 to +85	FCC, ISCED, CE, UKCA, \MIC, & Bluetooth® SIG (in dev)	SMD	LGA	Single antenna pin	SDIO, GSPI	UART, SDIO, SPI
CYW55512	Wi-Fi 6/6E (802.11ax)	u-blox	MAYA-W361	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	10.4 x 14.3 x 1.9	-40 to +85	FCC, ISCED, CE, UKCA, \MIC, & Bluetooth® SIG (in dev)	SMD	LGA	2 antenna pins	SDIO, GSPI	UART, SDIO, SPI
CYW55512	Wi-Fi 6/6E (802.11ax)	u-blox	MAYA-W366	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	10.4 x 14.3 x 1.9	-40 to +85	FCC, ISCED, CE, UKCA, MIC, & Bluetooth® SIG (in dev)	SMD	LGA	PCB antenna	SDIO, GSPI	UART, SDIO, SPI
CYW55512	Wi-Fi 6/6E (802.11ax)	USI	WM-CW-55	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 6.1	8.6 x 8.1 x 1.1	-40 to +85	N/A	SMD	LGA	N/A	SDIO	UART
CYW55512	Wi-Fi 6/6E (802.11ax)	USI	WM-CW-55M	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 6.1	12 x 12 x 1.8	-40 to +85	N/A	SMD	LGA	N/A	SDIO	UART
CYW55532	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XM718-SD	2.4/5/6 GHz	1T1R	N/A	12 x 12 x 1.65	-40 to +85	FCC	SMD	LGA	-	SDIO	NA
CYW55532	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XM718-USB	2.4/5/6 GHz	1T1R	N/A	12 x 12 x 1.65	-40 to +85	FCC	SMD	LGA	-	USB	NA
CYW55511	Wi-Fi 6/6E (802.11ax)	u-blox	MAYA-W333	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	10.4 x 14.3 x 1.9	-40 to +85	FCC, ISCED, CE, UKCA, MIC, & Bluetooth® SIG (in dev)	SMD	LGA	Single antenna pin	SDIO, GSPI	UART, SDIO, SPI
CYW55511	Wi-Fi 6/6E (802.11ax)	u-blox	MAYA-W331	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	10.4 x 14.3 x 1.9	-40 to +85	FCC, ISCED, CE, UKCA, MIC, & Bluetooth® SIG (in dev)	SMD	LGA	2 antenna pins	SDIO, GSPI	UART, SDIO, SPI
CYW55511	Wi-Fi 6/6E (802.11ax)	u-blox	MAYA-W336	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	10.4 x 14.3 x 1.9	-40 to +85	FCC, ISCED, CE, UKCA, MIC, & Bluetooth® SIG (in dev)	SMD	LGA	PCB antenna	SDIO, GSPI	UART, SDIO, SPI

Wi-Fi 6/6E (802.11ax) + Dual-Mode Bluetooth® combo partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	Dim (xyz-mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW55571	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XB325MA-PUR	2.4/5/ 6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.3	22 x 30 x 2.06	-40 to +85	Follow AW-XH325's FCC	M.2 plug-in	M.2 2230	Ext. antenna by MHF4 connectors	PCIe	UART
CYW55571	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XB325MA-SUR	2.4/5/ 6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.3	22 x 30 x 2.06	-40 to +85	Follow AW-XH325's FCC	M.2 plug-in	M.2 2230	Ext. antenna by MHF4 connectors	SDIO	UART
CYW55571	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XH325-PUR	2.4/5/ 6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.3	10 x 10 x 1.26	-40 to +85	AW-XH323-xxx, AW-XH325-xxx and AW-XH327-xxx share the same FCC	SMD	SiP	RF pad	PCIe	UART
CYW55571	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XH325-SUR	2.4/5/ 6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.3	10 x 10 x 1.26	-40 to +85	AW-XH323-xxx, AW-XH325-xxx and AW-XH327-xxx share the same FCC	SMD	SiP	RF pad	SDIO	UART
CYW55571	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XM632-PUR	2.4/5/ 6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.3	12 x 12 x 1.9	-40 to +85	TBD	SMD	LGA	RF pad	PCIe	UART
CYW55571	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XM632-SUR	2.4/5/ 6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.3	12 x 12 x 1.9	-40 to +85	TBD	SMD	LGA	RF pad	SDIO	UART
CYW55571	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XM632-SURX	2.4/5/ 6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.3	10 x 10 x 1.26	-40 to +85	TBD	SMD	LGA	RF pad	SDIO	UART, I²S, PCM
CYW55571	Wi-Fi 6/6E (802.11ax)	Murata	LBEE5XV2EC-001	2.4/5/ 6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.3	12.5 x 9.4 x 1.2	-40 to +85	FCC/IC/CE/TELEC	SMD	LGA	Dipole ANT, monopole Trace ANT	SDIO, PCIe	UART, I²S, PCM
CYW55571	Wi-Fi 6/6E (802.11ax)	USI	WM-CW-51MS	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 6.0	12 x 16 x 1.8	-40 to +85	FCC/IC/TELEC	SMD	LGA (Metal Shielding on PCB)	IPEX Connector	SDIO/ PCIe	UART
CYW88570C	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XH326-PUR	2.4/5/ 6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	10 x 10 x 1.26	-40 to +85	TBD	SMD	SiP	RF pad	PCIe	UART, I²S, PCM
CYW88570C	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XH326-SUR	2.4/5/ 6 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	10 x 10 x 1.26	-40 to +85	TBD	SMD	SiP	RF pad	SDIO	UART, I²S, PCM
CYW88570D	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XH328-PUR	2.4/5 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	10 x 10 x 1.26	-40 to +85	TBD	SMD	SiP	RF pad	PCIe	UART, I²S, PCM
CYW88570D	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XH328-SUR	2.4/5 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.3	10 x 10 x 1.26	-40 to +85	TBD	SMD	SiP	RF pad	SDIO	UART, I²S, PCM
CYW89570XR	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-XHA01	2.4/5/ 6 GHz	2T2R+RSDB	Bluetooth®/ Bluetooth® LE 5.3	19 x 13 x 1.26	-40 to +85	TBD	SMD	SiP	RF pad	PCIe	UART, I²S, PCM

Wi-Fi 5 (802.11ac) + Dual-Mode Bluetooth® combo partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	Dim (xyz-mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW54591	Wi-Fi 5 (802.11ac)	Azurewave	AW-CB511NF	2.4/5 GHz	2T2R+RSDB	Bluetooth®/ Bluetooth® LE 5.4	22 x 30 x 2.25	-40 to +85	TBD	M.2 plug-in	M.2 2230	Ext. Antenna by MHF4 connectors	PCIe	UART, PCM
CYW54591	Wi-Fi 5 (802.11ac)	Azurewave	AW-CB511NF-BPF	2.4/5 GHz	2T2R+RSDB	Bluetooth®/ Bluetooth® LE 5.4	22 x 30 x 2.25	-40 to +85	CE, FCC, IC, JP, AU NZ, NCC, Brazil, KR, China, Vietnam	M.2 plug-in	M.2 2230	Ext. Antenna by MHF4 connectors	PCIe	UART
CYW54591	Wi-Fi 5 (802.11ac)	Azurewave	AW-CM572-RSDB	2.4/5 GHz	2T2R+RSDB	Bluetooth®/ Bluetooth® LE 5.4	15 x 13 x 1.95	-40 to +85	TBD	SMD	LGA	RF pad	SDIO	UART, PCM
CYW54591	Wi-Fi 5 (802.11ac)	Azurewave	AW-CM590-RSDB	2.4/5 GHz	2T2R+RSDB	Bluetooth®/ Bluetooth® LE 5.4	15 x 13 x 1.95	-40 to +85	TBD	SMD	LGA	RF pad	PCIe	UART, PCM
CYW54591	Wi-Fi 5 (802.11ac)	Embedded Artists	EAR00373	2.4/5 GHz	-	Bluetooth®/ Bluetooth® LE 5.1	-	-	-	M.2 plug-in	E-key 2230	u.fl	-	-
CYW54591	Wi-Fi 5 (802.11ac)	Murata	LBEE5XV1XA-540	2.4/5 GHz	2T2R+RSDB	Bluetooth®/ Bluetooth® LE 5.1	11.4 x 8.9 x 1.4	-40 to +85	FCC/IC/CE/TELEC	SMD	LGA	Dipole ANT, monopole Trace ANT	PCIe	UART
CYW54591	Wi-Fi 5 (802.11ac)	Murata	LBEE5XV1XZ-892	2.4/5 GHz	2T2R+RSDB	Bluetooth®/ Bluetooth® LE 5.1	11.4 x 8.9 x 1.4	-40 to +85	FCC/IC/CE/TELEC	SMD	LGA	Dipole ANT, monopole Trace ANT	SDIO	UART
CYW54591	Wi-Fi 5 (802.11ac)	Quectel	FC80A	2.4/5 GHz	2T2R+RSDB	Bluetooth®/ Bluetooth® LE 5.2	15 x 13 x 2.2	-40 to +85	China (SRRC)/ FCC/IC/CE/RCM/ KC/JATE/TELEC	SMD	LCC stamp	2 x 2	SDIO	UART, PCM
CYW54590	Wi-Fi 5 (802.11ac)	Azurewave	AW-CM572	2.4/5 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.1	13 x 15 x 1.95	-40 to +85	TBD	SMD	LGA	RF pad	SDIO	UART, PCM
CYW54590	Wi-Fi 5 (802.11ac)	Azurewave	AW-CM590	2.4/5 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.4	13 x 15 x 1.95	-40 to +85	TBD	SMD	LGA	RF pad	PCIe	UART, PCM
CYW54590	Wi-Fi 5 (802.11ac)	Embedded Artists	EAR00414	2.4/5 GHz	-	Bluetooth®/ Bluetooth® LE 5.1	-	-	-	M.2 plug-in	E-key 2230	u.fl	-	-
CYW54590	Wi-Fi 5 (802.11ac)	Murata	LBEE5XV2BA-001	2.4/5 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.1	11.4 x 8.9 x 1.4	-40 to +85	FCC/IC/CE/TELEC	SMD	LGA	Dipole ANT, monopole Trace ANT	PCIe	UART
CYW54590	Wi-Fi 5 (802.11ac)	Murata	LBEE5XV2BZ-883	2.4/5 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.1	11.4 x 8.9 x 1.4	-40 to +85	FCC/IC/CE/TELEC	SMD	LGA	Dipole ANT, monopole Trace ANT	SDIO	UART
CYW43022	Wi-Fi 5 (802.11ac)	Azurewave	AW-AM617	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	12 x 12 x 1.75	-20 to +70	CE/FCC/IC	SMD	LGA	RF pad	SDIO	UART, PCM

Wi-Fi 5 (802.11ac) + Dual-Mode Bluetooth® combo partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	Dim (xyz-mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW43022	Wi-Fi 5 (802.11ac)	Embedded Artists	EAR00497	2.4/5 GHz	-	Bluetooth®/ Bluetooth® LE 5.4	-	-	-	M.2 plug-in	E-key 2230	u.fl		
CYW43022	Wi-Fi 5 (802.11ac)	Murata	LBEE5WV2GF-924	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	10 x 7.2 x 1.5	-20 to +70	FCC/IC/CE/ TELEC(Planning)	SMD	LGA	Dipole ANT, monopole Trace ANT	SDIO	UART
CYW43022	Wi-Fi 5 (802.11ac)	USI	WM-CW-22	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	7.9 x 7.3 x 1.1	-20 to +70	N/A	SMD	LGA (Molding SIP)	N/A	SDIO	UART
CYW43455	Wi-Fi 5 (802.11ac)	Azurewave	AW-CH303	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.3	7.9 x 7.3 x 1	-30 to +85	N/A	SMD	SiP	RF pad	SDIO	UART
CYW43455	Wi-Fi 5 (802.11ac)	Azurewave	AW-CM256SM	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.3	12 x 12 x 1.5	-30 to +85	SRRC	SMD	Stamp LGA	RF pad	SDIO	UART
CYW43455	Wi-Fi 5 (802.11ac)	Azurewave	AW-CM390SM	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.3	12 x 12 x 1.50	-30 to +85	CE, FCC, IC, AU/NZ	SMD	Stamp LGA	RF pad	SDIO	UART
CYW43455	Wi-Fi 5 (802.11ac)	Iton	CW2455-44	2.4/5 GHz	1T1R	Bluetooth® LE 5.3	12 x 12	-40 to +85	FCC/CE/SRRC ROHS/BQB	SMD	PCB Module	External antenna	SDIO	UART, PCM
CYW43455	Wi-Fi 5 (802.11ac)	USI	WM-BAC-BM-25	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.3	9.5 x 15 x 1.8	-30 to +85	FCC/CE/IC/JPN	SMD	LGA (Metal Shielding on PCB)	Chip antenna	SDIO	UART
CYW43455	Wi-Fi 5 (802.11ac)	USI	WM-BAC-BM-28	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.3	7.9 x 7.3 x 1.1	-30 to +85	N/A	SMD	LGA (Molding SIP)	N/A	SDIO	UART
CYW4354	Wi-Fi 5 (802.11ac)	USI	WM-BAC-CYW-54	2.4/5 GHz	2T2R	Bluetooth®/ Bluetooth® LE 5.1	9.8 x 9 x 1.1	-30 to +85	N/A	SMD	LGA (Molding SIP)	N/A	SDIO	UART
CYW4373	Wi-Fi 5 (802.11ac)	Iton	IW4373-50B1	2.4/5 GHz	1T1R	Bluetooth® LE 5.4	26 x 20	-40 to +85	FCC/CE/SRRC/ ROHS/BQB	SMD	PCB Module	External antenna	SDIO	UART, PCM
CYW4373	Wi-Fi 5 (802.11ac)	Quectel	FC906A	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 12 x 1.55	-20 to +70	China (SRRC)/FCC/ IC/CE/RCM	SMD	LCC stamp	1 x 1	SDIO	UART, PCM
CYW4373	Wi-Fi 5 (802.11ac)	Quectel	FCU906A	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 12 x 1.55	-20 to +70	China (SRRC)/FCC/ IC/CE/RCM	SMD	LCC stamp	1 x 1	USB	USB, PCM
CYW4373E	Wi-Fi 5 (802.11ac)	Azurewave	AW-CM467-SUR-I	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 12 x 1.65	-40 to +85	CE, FCC, IC, NCC, AU/NZ, Japan, Korea, China	SMD	LGA	RF pad	SDIO	UART

Wi-Fi 5 (802.11ac) + Dual-Mode Bluetooth® combo partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	Dim (xyz-mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW4373E	Wi-Fi 5 (802.11ac)	Azurewave	AW-CM467-USB-I	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 12 x 1.65	-40 to +85	CE, FCC, IC, NCC, AU/NZ, Japan, Korea, China	SMD	LGA	RF pad	USB	USB
CYW4373E	Wi-Fi 5 (802.11ac)	Azurewave	AW-CM688	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 12 x 1.75	-40 to +85	FCC	SMD	LGA	RF pad	USB	USB
CYW4373E	Wi-Fi 5 (802.11ac)	Embedded Artists	EAR00388	2.4/5 GHz		Bluetooth®/ Bluetooth® LE 5.2	-	-	-	M.2 plug-in	E-key 2244	Integrated trace antenna	-	-
CYW4373E	Wi-Fi 5 (802.11ac)	Ezurio	450-00137	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	17 x 47 x 11.7	-40 to +85	FCC, ISCED, CE, MIC, UKCA, KCC, TW, BR, CN, RCM Bluetooth® SIG	USB adapter	-	Integrated antenna	USB	-
CYW4373E	Wi-Fi 5 (802.11ac)	Ezurio	450-00137B	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	17 x 47 x 11.7	-40 to +85	FCC, ISCED, CE, MIC, UKCA, KCC, TW, BR, CN, RCM Bluetooth® SIG	USB adapter	-	Integrated antenna	USB	-
CYW4373E	Wi-Fi 5 (802.11ac)	Ezurio	453-00045C	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 17 x 2.2	-40 to +85	FCC, ISCED, CE, MIC, UKCA, KCC, TW, BR, CN, RCM Bluetooth® SIG	SMD	LGA	Integrated chip antenna (Cut Tape)	UART, SDIO, USB	-
CYW4373E	Wi-Fi 5 (802.11ac)	Ezurio	453-00045-K1	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 17 x 2.2	-40 to +85	FCC, ISCED, CE, MIC, UKCA, KCC, TW, BR, CN, RCM Bluetooth® SIG	SMD	LGA	Integrated chip antenna (Cut Tape)	UART, SDIO, USB	-
CYW4373E	Wi-Fi 5 (802.11ac)	Ezurio	453-00045R	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 17 x 2.2	-40 to +85	FCC, ISCED, CE, MIC, UKCA, KCC, TW, BR, CN, RCM Bluetooth® SIG	SMD	LGA	Integrated chip antenna (Cut Tape)	UART, SDIO, USB	-
CYW4373E	Wi-Fi 5 (802.11ac)	Ezurio	453-00046C	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 17 x 2.2	-40 to +85	FCC, ISCED, CE, MIC, UKCA, KCC, TW, BR, CN, RCM Bluetooth® SIG	SMD	LGA	MHF4 antenna (Cut Tape)	UART, SDIO, USB	-
CYW4373E	Wi-Fi 5 (802.11ac)	Ezurio	453-00046-K1	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 17 x 2.2	-40 to +85	FCC, ISCED, CE, MIC, UKCA, KCC, TW, BR, CN, RCM Bluetooth® SIG	SMD	LGA	MHF4 antenna (Cut Tape)	UART, SDIO, USB	-
CYW4373E	Wi-Fi 5 (802.11ac)	Ezurio	453-00046R	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 17 x 2.2	-40 to +85	FCC, ISCED, CE, MIC, UKCA, KCC, TW, BR, CN, RCM Bluetooth® SIG	SMD	LGA	MHF4 (Tape & Reel)	UART, SDIO, USB	-
CYW4373E	Wi-Fi 5 (802.11ac)	Ezurio	453-00047C	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 17 x 2.2	-40 to +85	FCC, ISCED, CE, MIC, UKCA, KCC, TW, BR, CN, RCM Bluetooth® SIG	SMD	LGA	RF Trace Pin (Cut Tape)	UART, SDIO, USB	-
CYW4373E	Wi-Fi 5 (802.11ac)	Ezurio	453-00047R	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 17 x 2.2	-40 to +85	FCC, ISCED, CE, MIC, UKCA, KCC, TW, BR, CN, RCM Bluetooth® SIG	M.2 plug-in	E-key 2230	RF Trace Pin (Tape and Reel)	UART, SDIO, USB	-
CYW4373E	Wi-Fi 5 (802.11ac)	Ezurio	453-00048	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	22 x 30 x 3.1	-40 to +85	FCC, ISCED, CE, MIC, UKCA, KCC, TW, BR, CN, RCM Bluetooth® SIG	M.2 plug-in	E-key 2230	MHF4	UART, SDIO	

Wi-Fi 5 (802.11ac) + Dual-Mode Bluetooth® combo partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	Dim (xyz-mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW4373E	Wi-Fi 5 (802.11ac)	Ezurio	453-00048-K1	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	22 x 30 x 3.1	-40 to +85	FCC, ISCED, CE, MIC, UKCA, KCC, TW, BR, CN, RCM Bluetooth® SIG	DVK	M.2 plug-in	MHF4	SDIO	-
CYW4373E	Wi-Fi 5 (802.11ac)	Ezurio	453-00049	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	22 x 30 x 3.1	-40 to +85	FCC, ISCED, CE, MIC, UKCA, KCC, TW, BR, CN, RCM Bluetooth® SIG	M.2 plug-in	E-key 2230	MHF4	USB	-
CYW4373E	Wi-Fi 5 (802.11ac)	Ezurio	453-00049-K1	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	22 x 30 x 3.1	-40 to +85	FCC, ISCED, CE, MIC, UKCA, KCC, TW, BR, CN, RCM Bluetooth® SIG	M.2 plug-in	E-key 2230	MHF4	USB	-
CYW4373E	Wi-Fi 5 (802.11ac)	Murata	LBEE5PK2AE-564	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	8.0 x 7.8 x 1.15	-40 to +85	FCC/IC/CE/TELEC	SMD	LGA	Dipole ANT, monopole Trace ANT	SDIO, USB	UART, USB
CYW4373I	Wi-Fi 5 (802.11ac)	Azurewave	AW-CM467-SUR	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 12 x 1.65	-20 to +70	CE, FCC, IC, NCC, AU/NZ, JP, KR, China	SMD	LGA	RF pad	SDIO	UART
CYW4373I	Wi-Fi 5 (802.11ac)	Azurewave	AW-CM467-USB	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 12 x 1.65	-20 to +70	CE, FCC, IC, NCC, AU/NZ, Japan, Korea, China	SMD	LGA	RF pad	USB	USB
CYW4373I	Wi-Fi 5 (802.11ac)	Azurewave	AW-CM555-SUR	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 12 x 1.65	-20 to +70	FCC/CE	SMD	LGA	RF pad	SDIO	UART, PCM
CYW4373I	Wi-Fi 5 (802.11ac)	Embedded artists	EAR00436	2.4/5 GHz	-	Bluetooth®/ Bluetooth® LE 5.2	-	-	-	M.2 plug-in	E-key 2244	Integrated trace antenna		
CYW4373I	Wi-Fi 5 (802.11ac)	Murata	LBEE5PK2BC-771	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	8.0 x 7.8 x 1.15	-20 to +70	FCC/IC/CE/TELEC	SMD	LGA	Dipole ANT, monopole Trace ANT	SDIO, USB	UART, USB
CYW88373	Wi-Fi 5 (802.11ac)	Azurewave	AW-CM605	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 12 x 1.65	-40 to +85	TBD	SMD	LGA	RF pad	SDIO	UART
CYW88373	Wi-Fi 5 (802.11ac)	Azurewave	AW-CMA02	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	22 x 22 x 2.30	-40 to +85	TBD	SMD	LGA	RF pad	PCIe	UART, I²S, PCM

Wi-Fi 4 (802.11n) + Dual-Mode Bluetooth® combo partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	Dim (xyz-mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW43012	Wi-Fi 4 (802.11n)	Alinket	ALX850	2.4/5 GHz	1T1R	N/A	28 x 14.3 x 2.2	-30 to +85	FCC/CE/RoHS	SMD	SIP on FR4	On-Board or External antenna U.FL	SDIO	-
CYW43012	Wi-Fi 4 (802.11n)	Alinket	ALXC20B	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 4.2	28 x 14.3 x 2.2	-30 to +85	FCC/CE/RoHS	SMD	SiP on FR4	On-Board or External antenna U.FL	SDIO	UART, SPI, I²S
CYW43012	Wi-Fi 4 (802.11n)	Azurewave	AW-AM497	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 12 x 1.75	-20 to +70	CE/FCC/IC	SMD	LGA	RF pad	SDIO	UART, PCM
CYW43012	Wi-Fi 4 (802.11n)	Azurewave	AW-AH306	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	8.5 x 7 x 1.21	-20 to +70	N/A	SMD	SIP	RF pad	SDIO	UART
CYW43012	Wi-Fi 4 (802.11n)	Azurewave	AW-AM689	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	12 x 12 x 1.75	-20 to +70	N/A	SMD	LGA	RF pad	SDIO	UART
CYW43012	Wi-Fi 4 (802.11n)	Embedded Artists	EAR00323	2.4/5 GHz	-	Bluetooth®/ Bluetooth® LE 5.2	-	-	-	M.2 plug-in	E-key 2244	Integrated trace antenna	-	-
CYW43012	Wi-Fi 4 (802.11n)	Iton	IW3012-44B1	2.4/5 GHz	1T1R	Bluetooth® LE 5.2	12 x 12	-40 to +85	FCC/CE/SRRC/ROHS/ BQB	SMD	PCB Module	External antenna	SDIO	UART, PCM
CYW43012	Wi-Fi 4 (802.11n)	Murata	LBEE59B1LV-278	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	10 x 7.2 x 1.4	-20 to +70	FCC/IC/CE/TELEC	SMD	LGA	Monopole Trace ANT	SDIO	UART
CYW43439	Wi-Fi 4 (802.11n)	Azurewave	AW-NM512	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 12 x 1.5	-30 to +85	CE/FCC/IC/NCC	SMD	LGA	RF pad	SDIO	UART, PCM
CYW43439	Wi-Fi 4 (802.11n)	Embedded Artists	EAR00389	2.4 GHz	-	Bluetooth®/ Bluetooth® LE 5.2	-	-	-	M.2 plug-in	E-key 2244	Integrated trace antenna	-	-
CYW43439	Wi-Fi 4 (802.11n)	Ezurio	453-00083C	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 12 x 3	-40 to +85	FCC, ISCED, CE, UKCA, MIC, RCM, KCC, BR & Bluetooth® SIG	SMD	SIP	RF Trace antenna (Cut Tape)	UART SDIO, I²S	-
CYW43439	Wi-Fi 4 (802.11n)	Ezurio	453-00083R	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 12 x 3	-40 to +85	FCC, ISCED, CE, UKCA, MIC, RCM, KCC, BR & Bluetooth® SIG	SMD	SIP	RF Trace antenna (Tape & Reel)	UART SDIO, I²S	-
CYW43439	Wi-Fi 4 (802.11n)	Ezurio	453-00084C	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	21 x 15 x 4	-40 to +85	FCC, ISCED, CE, UKCA, MIC, RCM, KCC, BR & Bluetooth® SIG	SMD	LGA	MHF4 antenna (Cut Tape)	UART SDIO, I²S	-
CYW43439	Wi-Fi 4 (802.11n)	Ezurio	453-00084-K1	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	21 x 15 x 4	-40 to +85	FCC, ISCED, CE, UKCA, MIC, RCM, KCC, BR & Bluetooth® SIG	SMD	LGA	MHF4 antenna (Cut Tape)	UART SDIO, I²S	-

Wi-Fi 4 (802.11n) + Dual-Mode Bluetooth® combo partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	Dim (xyz-mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW43439	Wi-Fi 4 (802.11n)	Ezurio	453-00084R	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	21 x 15 x 4	-40 to +85	FCC, ISCED, CE, UKCA, MIC, RCM, KCC, BR & Bluetooth® SIG	SMD	LGA	MHF4 antenna (Tape & Reel)	UART SDIO, I²S	-
CYW43439	Wi-Fi 4 (802.11n)	Ezurio	453-00085C	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	21 x 15 x 4	-40 to +85	FCC, ISCED, CE, UKCA, MIC, RCM, KCC, BR & Bluetooth® SIG	SMD	LGA	Onboard chip antenna (Cut Tape)	UART SDIO, I²S	-
CYW43439	Wi-Fi 4 (802.11n)	Ezurio	453-00085-K1	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	21 x 15 x 4	-40 to +85	FCC, ISCED, CE, UKCA, MIC, RCM, KCC, BR & Bluetooth® SIG	SMD	LGA	Onboard chip antenna (Cut Tape)	UART SDIO, I²S	-
CYW43439	Wi-Fi 4 (802.11n)	Ezurio	453-00085R	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	21 x 15 x 4	-40 to +85	FCC, ISCED, CE, UKCA, MIC, RCM, KCC, BR & Bluetooth® SIG	SMD	LGA	Onboard chip antenna (Tape & Reel)	UART SDIO, I²S	-
CYW43439	Wi-Fi 4 (802.11n)	Ezurio	453-00141	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	22 x 30	-40 to +85	FCC, ISCED, CE, UKCA, MIC, RCM, KCC, BR & Bluetooth® SIG	M.2 plug-in	E-key 2230	MHF4 antenna (Carton)	UART SDIO, I²S	-
CYW43439	Wi-Fi 4 (802.11n)	INVENTEK (USA Company)	ISM43439-WBP L151	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	10 x 10 x 1.2	-40 to +85	Certification Pending	-	-	Chip or U.FL external antenna	UART, SDIO, I²S PCM	-
CYW43439	Wi-Fi 4 (802.11n)	Murata	LBEE5L1YN-814	2.4 GHz	1T1R	Bluetooth® LE 5.2	6.95 x 5.15 x1.1	-30 to +70	FCC/IC/CE/ TELEC	SMD	v	Dipole ANT, monopole Trace ANT	SDIO	UART, PCM
CYW43439	Wi-Fi 4 (802.11n)	Quectel	FC909A	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 12 x 1.95	-30 to +85	China (SRRC)/FCC/ CE/IC	SMD	LCC stamp	1 x 1	SDIO	UART, PCM
CYW43439	Wi-Fi 4 (802.11n)	USI	IS1	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	12 x 11 x 1.3	-30 to +70	N/A	SMD	LGA (Metal Shielding on PCB)	Antenna connector only	Configurable external I/O	Configurable external I/O
CYW43439	Wi-Fi 4 (802.11n)	USI	WM-CW-26	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	9.5 x 15 x 1.8	-30 to +70	FCC/CE/JPN remark	SMD	LGA (Metal Shielding on PCB)	Chip antenna	SDIO	UART
CYW43438	Wi-Fi 4 (802.11n)	Alinket	ALXC12B	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 4.1	32 x 16 x 3.1	-30 to +85	FCC/CE/RoHS	SMD	SIP on FR4	On-Board or External antenna U.FL	SDIO	UART, SPI, I²S
CYW43438	Wi-Fi 4 (802.11n)	Azurewave	AW-NM197SM	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.1	12 x 12 x 1.5	-30 to +85	TBD	SMD	Stamp LGA	RF pad	SDIO	UART
CYW43438	Wi-Fi 4 (802.11n)	Azurewave	AW-NM372SM	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.1	12 x 12 x 1.5	-30 to +85	CE, FCC, SRRC, NCC	SMD	Stamp LGA	RF pad	SDIO	UART

Wi-Fi 4 (802.11n) + Dual-Mode Bluetooth® combo partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	Dim (xyz-mm)	Op. Temp (°C)	Regulatory	Type	Pa- ckage	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW43438	Wi-Fi 4 (802.11n)	Iton	IWCW2438-44	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	12 x 12 x 1.5	-40 to +85	-	SMD	Stamp LGA	Single antenna	-	PCM
CYW43438	Wi-Fi 4 (802.11n)	Murata	LBEE5PA1LD-005	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	8.9 x 7.8 x 1.2	-40 to +85	FCC/IC/CE/TELEC	SMD	LGA	Monopole Trace ANT	UART, SPI, I²C	UART, SPI, I²C
CYW4343	Wi-Fi 4 (802.11n)	INVENTEK (USA Company)	ISM4343-WBM-L151-U	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.1	10 x 10 x 1.2	-40 to +85	FCC/IC/CE/UKCA Additional Certs upon request	-	-	Chip or U.FL external antenna	UART, SPI, I²S, I²C, PCM, USB	-
CYW4343	Wi-Fi 4 (802.11n)	INVENTEK (USA Company)	ISM4343-WBM-L151	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.1	10 x 10 x 1.2	-40 to +85	FCC/IC/CE/UKCA Additional Certs upon request	-	-	Chip or U.FL external antenna	UART, SPI, I²S, PCM	-
CYW4343	Wi-Fi 4 (802.11n)	INVENTEK (USA Company)	ISM4343-WBM-L54	2.4 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.1	34.22 x 14.7 x 2.0	-40 to +85	FCC/IC/CE/UKCA Additional Certs upon request	-	-	Chip or U.FL external antenna	UART, SPI, I²S, PCM	-
CYW43362	Wi-Fi 4 (802.11n)	Alinket	ALX830	2.4 GHz	1T1R	N/A	28 x 14.3 x 2.2	-30 to +85	FCC/CE/RoHS	SMD	SIP	On-Board or External antenna U.FL	SDIO	N/A
CYW43362	Wi-Fi 4 (802.11n)	INVENTEK (USA Company)	ISM43362-M3G-L44	2.4 GHz	1T1R	N/A	34.22 x 14.7 x 2.3	-40 to +85	FCC/IC/CE/UKCA Additional Certs upon request	-	-	Etch/U.FL external antenna	UART, SPI, USB	N/A
CYW43340	Wi-Fi 4 (802.11n)	INVENTEK (USA Company)	ISM43340-L77	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.2	13 x 14.4 x 2.4	-40 to +85	FCC/IC/CE/UKCA Additional Certs upon request	-	-	Chip or U.FL external antenna	UART, SPI, SDIO, I²S, PCM	UART
CYW43340	Wi-Fi 4 (802.11n)	INVENTEK (USA Company)	ISM43340-M4G-L44	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	34.22 x 14.7 x 2.3	-40 to +85	FCC/IC/CE/UKCA Additional Certs upon request	-	-	Chip/U.FL external antenna	UART, SPI, I²S, PCM	-

Wi-Fi Connected MCU partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	CPU	Max Frequency	Flash	PSRAM	Dim (xyz- mm)	Op. Temp (°C)	Regula- tory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW55913	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-CU640	2.4/5/ 6 GHz	1T1R	Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	25 x 16 x 2.25	-40 to +85	CE, FCC	SMD	LGA	PCB antenna	N/A	N/A
CYW55913	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-CU668	2.4/5/ 6 GHz	1T1R	Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	12 x 12 x 1.75	-40 to +85	TBD	SMD	LGA	RF pad	N/A	N/A
CYW55913	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00400C	2.4/5/ 6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	7 x 11 x 1.4	-40 to +85	FCC,ISED, CE,UKCA, RCM, MIC,KCC & Bluetooth® SIG	-	SIP	RF trace antenna (Cut Tape)	SDIO	UART, I²S, PCM
CYW55913	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00400- K1	2.4/5/ 6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	80 x 70 x 10	-40 to +85	FCC,ISED, CE,UKCA, RCM, MIC,KCC & Bluetooth® SIG	DVK	SIP	-	SDIO	UART, I²S, PCM
CYW55913	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00400R	2.4/5/ 6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	7 x 11 x 1.4	-40 to +85	FCC,ISED, CE,UKCA, RCM, MIC,KCC & Bluetooth® SIG	-	SIP	RF trace antenna (Tape & Reel)	SDIO	UART, I²S, PCM
CYW55913	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00401C	2.4/5/ 6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	8MB	8MB	7 x 11 x 1.4	-40 to +85	FCC,ISED, CE,UKCA, RCM, MIC,KCC & Bluetooth® SIG	-	SIP	RF trace antenna (Cut Tape)	SDIO	UART, I²S, PCM
CYW55913	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00401R	2.4/5/ 6 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	8MB	8MB	7 x 11 x 1.4	-40 to +85	FCC,ISED, CE,UKCA, RCM, MIC,KCC & Bluetooth® SIG	-	SIP	RF trace antenna (Tape &Reel)	SDIO	UART, I²S, PCM
CYW55913	Wi-Fi 6/6E (802.11ax)	Quectel	FGMC63N	2.4/5/ 6 GHz	1T1R	Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	13 x 16 x 1.7	-40 to +85	SRRC/ ATE/ TELEC/ CE/ FCC/ IC RCM/	SMD	LGA	1 x 1	SDIO	UART

Wi-Fi Connected MCU partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	CPU	Max Frequency	Flash	PSRAM	Dim (xyz- mm)	Op. Temp (°C)	Regula- tory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW55913	Wi-Fi 6/6E (802.11ax)	USI	WM-CW-65U	2.4/5/ 6 GHz	1T1R	Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	8.6 x 8.1 x 1.1	-40 to +85	N/A	SMD	LGA (Molding SIP)	N/A	Configurable external I/O	Configurable external I/O
CYW55913	Wi-Fi 6/6E (802.11ax)	USI	WM-CW- 65UM	2.4/5/ 6 GHz	1T1R	Bluetooth® LE 5.4	Arm® Cortex® z-M33	192 MHz	N/A	N/A	15 x 15 x 2	-40 to +85	N/A	SMD	LGA (Metal Shielding on PCB)	N/A	Configurable external I/O	Configurable external I/O
CYW55912	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-CU642	2.4/ 5 GHz	1T1R	Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	25 x 16 x 2.25	-40 to +85	CE, FCC	SMD	LGA	PCB antenna	N/A	N/A
CYW55912	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-CU680	2.4/ 5 GHz	1T1R	Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	12 x 12 x 1.75	-40 to +85	CE, FCC	SMD	LGA	RF pad	N/A	N/A
CYW55912	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00396C	2.4/ 5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	7 x 11 x 1.4	-40 to +85	FCC,ISED, CE,UKCA, RCM, MIC,KCC & Bluetooth® SIG	SMD	SIP	RF trace antenna (Cut Tape)	SDIO	UART, I²S, PCM
CYW55912	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00396- K1	2.4/ 5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	80 x 70 x 10	-40 to +85	FCC,ISED, CE,UKCA, RCM, MIC,KCC & Bluetooth® SIG	DVK	SIP	RF trace antenna (Cut Tape)	SDIO	UART, I²S, PCM
CYW55912	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00396R	2.4/ 5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	7 x 11 x 1.4	-40 to +85	FCC,ISED, CE,UKCA, RCM, MIC,KCC & Bluetooth® SIG	SMD	SIP	RF trace antenna (Tape &Reel)	SDIO	UART, I²S, PCM
CYW55912	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00397C	2.4/ 5 GHz	1T1R	Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	8MB	8MB	7 x 11 x 1.4	-40 to +85	FCC,ISED, CE,UKCA, RCM, MIC,KCC & Bluetooth® SIG	-	SIP	RF trace antenna (Cut Tape)	SDIO	UART, I²S, PCM

Wi-Fi Connected MCU partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	CPU	Max Frequency	Flash	PSRAM	Dim (xyz- mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW55912	Wi-Fi 6/6E (802.11ax)	Ezurio	453-00397R	2.4/ 5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	8MB	8MB	7 x 11 x 1.4	-40 to +85	FCC, ISCED, CE, UKCA, RCM, MIC, KCC & Bluetooth® SIG	-	SiP	RF trace antenna (Tape & Reel)	SDIO	UART, I²S, PCM
CYW55912	Wi-Fi 6/6E (802.11ax)	Quectel	FGMC62N	2.4/ 5 GHz	1T1R	Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	13 x 16 x 1.7	-40 to +85	SRRC JATE/ TELEC/ CE FCC/ IC/ RCM/	SMD	LGA	1 x 1	SDIO	UART
CYW55912	Wi-Fi 6/6E (802.11ax)	USI	WM-CW- 55U	2.4/ 5 GHz	1T1R	Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	8.6 x 8.1 x 1.1	-40 to +85	N/A	SMD	LGA (Molding SiP)	N/A	Configurable external I/O	Configurable external I/O
CYW55912	Wi-Fi 6/6E (802.11ax)	USI	WM-CW- 55UM	2.4/ 5 GHz	1T1R	Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	12 x 12 x 1.8	-40 to +85	N/A	SMD	LGA (Metal Shielding on PCB)	N/A	Configurable external I/O	Configurable external I/O
CYW55912	Wi-Fi 6/6E (802.11ax)	USI	WM-CW- 55UMA	2.4/ 5 GHz	1T1R	Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	19 x 20 x 3	-40 to +85	N/A	-	LGA (Metal Shielding on PCB)	IPEX connector	Configurable external I/O	Configurable external I/O
CYW55911	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-CU699	2.4 GHz	1T1R	Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	25 x 16 x 2.25	-40 to +85	CE, FCC	SMD	LGA	PCB antenna	SDIO/SPI	UART
CYW55911	Wi-Fi 6/6E (802.11ax)	Azurewave	AW-CU712	2.4 GHz	1T1R	Bluetooth® LE 5.4	Arm® Cortex® -M33	192 MHz	N/A	N/A	12 x 12 x 1.75	-40 to +85	CE, FCC	SMD	LGA	RF pad	SDIO/SPI	UART
CYW43907	Wi-Fi 4 (802.11n)	INVENTEK (USA Company)	ISM43907R- WBM- L170	2.4/ 5 GHz	1T1R	N/A	Arm® Cortex® -R4	160 MHz	N/A	2MB	11 x 11 x 1.2	-40 to +85	Certifications upon request	-	-	No certified antenna	UART, SPI, I²S, I²C, Ethernet	N/A

Wi-Fi Connected MCU partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	CPU	Max Frequency	Flash	PSRAM	Dim (xyz- mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW43907	Wi-Fi 4 (802.11n)	INVENTEK (USA Company)	ISM43907- WM-L170	2.4/5 GHz	1T1R	N/A	Arm® Cortex® -R4	160 MHz	N/A	2MB	11 x 11 x .2	-40 to +85	FCC/IC/CE/ UKCA Additional Certs upon request	-	-	No certified antenna	UART, SPI, I²S	N/A
CYW43907	Wi-Fi 4 (802.11n)	Lantronix	XPC250 100B-02	2.4/5 GHz	1T1R	N/A	Arm® Cortex® -R4	160 MHz	N/A	N/A	25 x 17	-40 to +85	FCC/IC/ CE/TELEC/ SRRC	-	-	Dual U.FL	UART, SPI, SDIO, I²C, GPIO,USB, Ethernet	
CYW43907	Wi-Fi 4 (802.11n)	Lantronix	XPC250 200B-02	2.4/5 GHz	1T1R	N/A	Arm® Cortex® -R4	160 MHz	N/A	N/A	25 x 17	-40 to +85	FCC/IC/ CE/TELEC/ SRRC	-	-	ON- MODULE ANT	UART, SPI, SDIO, I²C, GPIO,USB, Ethernet	-
CYW43907	Wi-Fi 4 (802.11n)	Lantronix	XPC250 300B-02	2.4/5 GHz	1T1R	N/A	Arm® Cortex® -R4	160 MHz	N/A	N/A	25 x 17	-40 to +85	FCC/IC/ CE/TELEC/ SRRC	-	-	Dual U.FL	UART, SPI, SDIO, I²C, GPIO,USB, Ethernet	-
CYW43907	Wi-Fi 4 (802.11n)	Lantronix	XPC250 400B-02	2.4/5 GHz	1T1R	N/A	Arm® Cortex® -R4	160 MHz	N/A	N/A	25 x 17	-40 to +85	FCC/IC/ CE/TELEC/ SRRC	-	-	ON- MODULE ANT	UART, SPI, SDIO, I²C, GPIO,USB, Ethernet	-
CYW43907	Wi-Fi 4 (802.11n)	Murata	LBWA1UZ 1GC-958	2.4/5 GHz	1T1R	N/A	Arm® Cortex® -R4	160 MHz	N/A	N/A	10 x 10 x 1.2	-30 to +85	FCC/IC/ CE/TELEC	SMD	LGA	Monopole Trace ANT	UART, SPI, I²C, I²S, USB, Ethernet	N/A
CYW43907	Wi-Fi 4 (802.11n)	Murata	LBWA1UZ 1GC-901	2.4/5 GHz	1T1R	N/A	Arm® Cortex® -R4	160 MHz	N/A	N/A	10 x 10 x 1.2	-30 to +85	FCC/IC/ CE/TELEC	SMD	LGA	Monopole Trace ANT	UART, SPI, I²C, I²S, USB, Ethernet	N/A
CYW54907	Wi-Fi 5 (802.11ac)	INVENTEK (USA Company)	ISM54907- WBM-L170	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 4.2	Arm® Cortex® -R4	160 MHz	N/A	N/A	11 x 11 x .2	-40 to +85	Certifications upon request	-	-	No certified antenna	UART, SPI, USB	-

Wi-Fi Connected MCU partner module portfolio

Wi-Fi/ Bluetooth® PN	Wi-Fi Specification	Partner	PN Module	Wi-Fi Band	WLAN Stream	Bluetooth®/ Bluetooth® Low Energy Specification	CPU	Max Frequency	Flash	PSRAM	Dim (xyz- mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Wi-Fi Interface	Bluetooth® Interface
CYW54907	Wi-Fi 5 (802.11ac)	Lantronix	XPC270100B	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 4.2	Arm® Cortex® -R4	160 MHz	N/A	N/A	25 x 17	-40 to +85	FCC/IC/CE	-	-	Dual U.FL	UART, SPI, SDIO, I²C, GPIO, USB, Ethernet	-
CYW54907	Wi-Fi 5 (802.11ac)	Lantronix	XPC270100S	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 4.2	Arm® Cortex® -R4	160 MHz	N/A	N/A	25 x 17	-40 to +85	FCC/IC/CE	-	-	Dual U.FL	UART, SPI, SDIO, I²C, GPIO, USB, Ethernet	-
CYW54907	Wi-Fi 5 (802.11ac)	Lantronix	XPC270300B	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 4.2	Arm® Cortex® -R4	160 MHz	N/A	N/A	35 x 22	-40 to +85	FCC/IC/CE	-	-	Dual U.FL	UART, SPI, SDIO, I²C, GPIO, USB, Ethernet	-
CYW54907	Wi-Fi 5 (802.11ac)	Lantronix	XPC270300S	2.4/5 GHz	1T1R	Bluetooth®/ Bluetooth® LE 4.2	Arm® Cortex® -R4	160 MHz	N/A	N/A	25 x 17	-40 to +85	FCC/IC/CE	-	-	Dual U.FL	UART, SPI, SDIO, I²C, GPIO, USB, Ethernet	-
CYW54907	Wi-Fi 5 (802.11ac)	Murata	LBWA1UZ1PS -241	2.4/5 GHz	1T1R	N/A	Arm® Cortex® -R4	160 MHz	N/A	N/A	10 x 10 x 1.2	-30 to +50	FCC/IC/CE/ TELEC	SMD	LGA	Monopole Trace ANT	UART, SPI, I²C, I²S, USB, Ethernet	N/A

Bluetooth® & Bluetooth® Low Energy (Dual-Mode) partner module portfolio

Bluetooth® PN	Partner	PN Module	Bluetooth®/Bluetooth® Low Energy Specification	Dim (xyz-mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Bluetooth® Interface
CYW55310	Azurewave	AW-BT728	Bluetooth®/Bluetooth® LE 5.3	12 x 12 x 1.85	-40 to +85	N/A	SMD	LGA	RF pad	UART, I²S, PCM
CYW55310	Ezurio	453-00390C	Bluetooth®/Bluetooth® LE 6.0	12 x 16 x 2	-40 to +85	FCC, ISCED, CE, UKCA, MIC, & Bluetooth® SIG	SMD	LGA	Integrated Ignion antenna	UART, I²S, PCM
CYW55310	Ezurio	453-00390-K1	Bluetooth®/Bluetooth® LE 6.0	12 x 16 x 2	-40 to +85	FCC, ISCED, CE, UKCA, MIC, & Bluetooth® SIG	DVK	LGA	Integrated Ignion antenna	UART, I²S, PCM
CYW55310	Ezurio	453-00390R	Bluetooth®/Bluetooth® LE 6.0	12 x 16 x 2	-40 to +85	FCC, ISCED, CE, UKCA, RCM, MIC, KCC & Bluetooth® SIG	SMD	LGA	Integrated Ignion antenna	UART, I²S, PCM
CYW55310	Ezurio	453-00391C	Bluetooth®/Bluetooth® LE 6.0	12 x 16 x 2	-40 to +85	FCC, ISCED, CE, UKCA, MIC, & Bluetooth® SIG	SMD	LGA	MHF4 connector	UART, I²S, PCM
CYW55310	Ezurio	453-00391-K1	Bluetooth®/Bluetooth® LE 6.0	12 x 16 x 2	-40 to +85	FCC, ISCED, CE, UKCA, MIC, & Bluetooth® SIG	DVK	LGA	MHF4 connector	UART, I²S, PCM
CYW55310	Ezurio	453-00391R	Bluetooth®/Bluetooth® LE 6.0	12 x 16 x 2	-40 to +85	FCC, ISCED, CE, UKCA, MIC, & Bluetooth® SIG	SMD	LGA	MHF4 connector	UART, I²S, PCM
CYW55310	Ezurio	453-00392C	Bluetooth®/Bluetooth® LE 6.0	12 x 16 x 2	-40 to +85	FCC, ISCED, CE, UKCA, MIC, & Bluetooth® SIG	SMD	LGA	Trace pin	UART, I²S, PCM
CYW55310	Ezurio	453-00392R	Bluetooth®/Bluetooth® LE 6.0	12 x 16 x 2	-40 to +85	FCC, ISCED, CE, UKCA, MIC, & Bluetooth® SIG	SMD	LGA	Trace pin	UART, I²S, PCM
CYW20829	Pairlink	Pony-B	Bluetooth® LE 5.4	23.0 x 14.0 x 2.6	-30 to +85	Ongoing	SMD	30 pad	Chip antenna	UART, SPI, I²C, PWM, CAN
CYW20829	Pairlink	Pony-C	Bluetooth® LE 5.4	23.0 x 14.0 x 2.6	-30 to +85	Ongoing	SMD	30 pad	IPEX connector	UART, SPI, I²C, PWM, CAN
CYW20835	Pairlink	Tigerkin-B8	Bluetooth® LE 5.4	23.0 x 14.0 x 2.6	-30 to +85	BQB\FCC\IC\CE\MIC\SRRC\RoHS	SMD	20 pad	Chip antenna	UART, SPI, I²C, PWM
CYW20835	Pairlink	Tigerkin-C8	Bluetooth® LE 5.4	23.0 x 14.0 x 2.6	-30 to +85	BQB\FCC\IC\CE\MIC\SRRC\RoHS	SMD	20 pad	IPEX connector	UART, SPI, I²C, PWM
CYW20820	Ezurio	453-00171C	Bluetooth®/Bluetooth® LE 5.4	12.5 x 9.3 x 2.15	-40 to +85	FCC\IC\CE\UKCE\RCM\MIC\KR\Bluetooth® SIG	SMD	LGA	-	UART, PCM, I²C, I²S, GPIO, SPI
CYW20820	Ezurio	453-00171R	Bluetooth®/Bluetooth® LE 5.4	12.5 x 9.3 x 2.15	-40 to +85	FCC\IC\CE\UKCE\RCM\MIC\KR\Bluetooth® SIG	SMD	LGA	-	UART, PCM, I²C, I²S, GPIO, SPI
CYW20820	Ezurio	453-00172C	Bluetooth®/Bluetooth® LE 5.4	7.5 x 7.5 x 2.15	-40 to +85	FCC\IC\CE\UKCE\RCM\MIC\KR\Bluetooth® SIG	SMD	LGA	-	UART, PCM, I²C, I²S, GPIO, SPI
CYW20820	Ezurio	453-00172R	Bluetooth®/Bluetooth® LE 5.4	7.5 x 7.5 x 2.15	-40 to +85	FCC\IC\CE\UKCE\RCM\MIC\KR\Bluetooth® SIG	SMD	LGA	-	UART, PCM, I²C, I²S, GPIO, SPI

Bluetooth® & Bluetooth® Low Energy (Dual-Mode) partner module portfolio

Bluetooth® PN	Partner	PN Module	Bluetooth®/Bluetooth® Low Energy Specification	Dim (xyz-mm)	Op. Temp (°C)	Regulatory	Type	Package	Antenna	Bluetooth® Interface
CYW20820	Ezurio	453-00185	Bluetooth®/Bluetooth® LE 5.4	50.74 x 18.39 x 11	-40 to +85	FCC/IC/CE/UKCE/RCM/MIC/KR/Bluetooth® SIG	SMD	LGA	-	UART, PCM, I²C, I²S, GPIO, SPI
CYW20736	Alinket	ALX411	Bluetooth® LE 4.0	19 x 13.5 x 1.8	-30 to +85	FCC/CE/RoHS	SMD	SiP on FR4	On-Board antenna	UART, SPI
CYW20736	INVENTEK (USA Company)	ISM20736S	Bluetooth®/Bluetooth® LE 5.2	6.5 x 6.5 x 1.18	-40 to +85	FCC/IC/CE	-	-	TBD	SPI, I²C
CYW20721	Murata	LBCA1KU1WA-427	Bluetooth®/Bluetooth® LE 5.1	5.1 x 5.9 x 1.1	-30 to +85	FCC/IC/CE/TELEC	SMD	-	Monopole Trace ANT, chip ANT	UART, PCM, I²C, SPI, I²C
CYW20706	Alinket	ALX420A	Bluetooth®/Bluetooth® LE 4.1	16 x 10 x 2.4	-30 to +85	FCC/CE/RoHS	SMD	-	On-Board antenna	UART, SPI, I²S
CYW20706	INVENTEK (USA Company)	ISM20706A2S	Bluetooth®/Bluetooth® LE 5.2	6.0 x 8.6 x 1.2	-40 to +85	Certifications upon request	-	-	Embedded antenna	SPI, I²C
CYW20706	Pairlink	Dragon-B	Bluetooth®/Bluetooth® LE 5.2	11 x 16.8 x 2.6	-30 to +85	BQB/MIC/FCC/IC/CE/ROHS	-	-	Chip antenna	UART, PWM, MFi, I²S
CYW20706	Pairlink	Dragon-C	Bluetooth®/Bluetooth® LE 5.2	11 x 16.8 x 2.6	-30 to +85	BQB/MIC/FCC/IC/CE/ROHS	-	-	IPEX connector	UART, PWM, MFi, I²S
CYW20704	Ezurio	BT-850-SA	Bluetooth®/Bluetooth® LE 5.0	8.5 x 12 x 2.2	-30 to +85	FCC/IC/CE/RCM/Giteki/KCC	-	-	Trace Pin Internal or external	USB, HCI, I²S, PCM, GPIO
CYW20704	Ezurio	BT-850-ST	Bluetooth®/Bluetooth® LE 5.0	8.5 x 13 x 1.9	-30 to +85	FCC/IC/CE/RCM/Giteki/KCC	-	-	Trace Pin Internal or external	USB, HCI, I²S, PCM, GPIO
CYW20704	Ezurio	BT-851	Bluetooth®/Bluetooth® LE 5.0	43 x 16 x 11	-30 to +85	FCC/IC/CE/RCM/Giteki/KCC	-	-	Trace Pin Internal or external	USB, HCI, I²S, PCM, GPIO
CYW20704	Ezurio	BT-860-SA	Bluetooth®/Bluetooth® LE 5.0	8.5 x 12.85	-30 to +85	FCC/IC/CE/RCM/Giteki/KCC	-	-	Trace Pin Internal or external	UART, HCI, I²S, PCM, GPIO
CYW20704	Ezurio	BT-860-ST	Bluetooth®/Bluetooth® LE 5.0	8.5 x 12.85 x 1.9	-30 to +85	FCC/IC/CE/RCM/Giteki/KCC	-	-	Trace Pin Internal or external	UART, HCI, I²S, PCM, GPIO
CYW89072	Azurewave	AW-BTA03	Bluetooth®/Bluetooth® LE 5.2	10 x 10 x 2.4	-40 to +85	N/A	SMD	LGA	RF pad	UART, I²S, PCM

Connectivity devices:

Wi-Fi + Bluetooth® Combo Devices
www.infineon.com/wi-fi-and-bluetooth-combos

Software and support:

ModusToolbox™ software environment
www.infineon.com/modustoolbox

Infineon Partner Network
www.infineon.com/partnerfinder

Infineon Developer Community
<https://community.infineon.com>

Wi-Fi MCU devices
www.infineon.com/wi-fi-mcu

Bluetooth® and Bluetooth® LE devices
www.infineon.com/airoc-bluetooth-le-bluetooth-multiprotocol

Technical forum for ModusToolbox™
www.infineon.com/modustoolbox-community

Technical forum for Linux
www.infineon.com/wi-fi-bluetooth-linux-drive-community



www.infineon.com

Published by Infineon Technologies AG
Am Campeon 1-15, 85579 Neubiberg
Germany

© 2026 Infineon Technologies AG.
All Rights Reserved.

Document Number: 002-33054 Rev. *E

Date: 08/2026

Please note!

This document is for information purposes only and any information given herein shall in no event be regarded as a warranty, guarantee or description of any functionality, conditions and/or quality of our products or any suitability for a particular purpose. With regard to the technical specifications of our products, we kindly ask you to refer to the relevant product data sheets provided by us. Our customers and their technical departments are required to evaluate the suitability of our products for the intended application.

We reserve the right to change this document and/or the information given herein at any time.

Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office (www.infineon.com).

Trademarks

All Referenced product or service names and trademarks are the property of their respective owners.

The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc., and any use of such marks by Infineon is under license.

Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any life-endangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.

Any sales transactions involving the partner modules referenced herein, including their terms and conditions, are between you and the partner.